

Part Number: **5611002090F**

| General Description |                                 |
|---------------------|---------------------------------|
|                     |                                 |
| Color               | Blue                            |
| Series              | 561                             |
| Configuration       | 5 mm Lens                       |
| Description         | 5 mm Stand - Off 0.900" WC Blue |
| Package Options     | Bulk Packaging                  |
| Sizes               | 5mm                             |
| Lamp Type           | Single Color                    |
| Viewing             | Top View                        |
| Polarity            | Cathode Right                   |
| Lens Style          | Non - Diffused                  |

| Absolute Maximum Ratings (Ta = 25Â° ) |                       |
|---------------------------------------|-----------------------|
|                                       |                       |
| Derating                              | from 40Â° @ .5 mA/Â°C |
| Solder Temperature                    | 260Â° for 5 sec       |
| Operating Temperature                 | -30 to +85            |
| Storage Temperature                   | -40 to +100           |

| Operating Characteristics  |                 |
|----------------------------|-----------------|
|                            |                 |
| Color                      | Blue            |
| LED Type                   | High Efficiency |
| Luminous Intensity Min     | 0.9             |
| Luminous Intensity Typical | 1.5             |
| Test Current mA            | 20mA            |
| Emitted Color              | Blue            |
| Power Dissipation Max      | 120mW           |



5611002090F

check stock



[This is a RoHS Compliant Product](#)  
[To learn more click here](#)