



Heyco® Straight-Thru Strain Relief Bushings

For Round Cables






WILL FIT THESE CABLES				PANEL DIMENSIONS						PART NO.		DESCRIPTION	C BODY LENGTH	
UL Type Designation	AWG/ Conductors	Approximate Diameter		A Mounting Hole Dia.		B To Prevent Rotation		Maximum Panel Thickness¹		Black	White		in.	mm.
		in.	mm.	in.	mm.	in.	mm.	in.	mm.					
AWM	—	.125-*.187	3,2-4,8	.375	9,5	.330	8,4	.062	1,6	1060	1061	SR 2M-1	.406	10,3
SV & SVT	18/2	.220-.245	5,6-6,2	.500	12,7	.450	11,4	.062	1,6	1157	1158	SR 5MN-3	.438	11,1
Same as SR 5MN-3 above except								.100	2,5	1140	1141	SR 5M-3	.438	11,1
SV & SVT	18/2	.250	6,4	.500	12,7									
	18/3	.255	6,5	.500-.515	12,7-13,1									
HPD	18/2	.270	6,9	.500	12,7									
	16/2	.290	7,4	.500-.515	12,7-13,1									
Same as SR 5N-4 above except								.100	2,5	1147	1148	SR 5P-4		
SV & SVT	18/3	.255	6,5									SR 5L-1		
HPD	16/2	.290	7,4										.156	4,0
SJ, SJT & SJO	18/2	.300	7,6	.500	12,7	.465	11,8	.090	2,3	1184	1185	SR 6W-1	.438	11,1
SJ, SJT & SJO	18/2	.300	7,6	.625	15,9	.550	14,0	.062	1,6	1217	1218	SR 6N-4	.578	14,7
Same as SR 6N-4 above except								.125	3,2	1210	1211	SR 6P-4	.578	14,7
SJ, SJT & SJO	16/2	.325	8,3											
	18/3	.330	8,4											
	14/2	.350	8,9											
	16/3	.355	9,0											
	18/4	.360	9,1											
Same as SR 6N3-4 above except								.125	3,2	1207	1208	SR 6P3-4	.578	14,7
SJ, SJT & SJO	18/2	.300	7,6	.625	15,9									
	16/2	.325	8,3	.656	16,7									
	18/3	.330	8,4	.656	16,7									
	16/3	.355	9,0	.687	17,4									

Standard Colors: Black or White. Consult Heyco for other colors.

*AWM cable only.

¹Maximum Panel Thickness—Part has additional clearance.



Material
Certifications

6/6 "Nylon"
Recognized under the Component Program of Underwriters' Laboratories
File #E-15331.

SP Certified by the Canadian Standards Association File #LR-8919

Flammability Rating

94V-2

Material Temperature Index

125°C—Maximum temperature on part not to exceed 105°C

Quick
Specs