



BMP™41 Label Printer

One and done



The BMP™41 Label printer is a rugged, **portable solution** that gives you the versatility to create die-cut or **continuous labels up to 25 mm wide**, anywhere, anytime! Whether you are faced with your jobs for the day or one-off tasks, the BMP™41 printer is the **one device for all your labelling jobs** - from wire marking and general ID to multi-area labels such as patch panel, terminal block and more.

Print it once, print it all, get it done!

Built to be rugged in any environment

- Drop-tested printer with rubber corner bumpers provide optimal protection and security from falls and wear and tear conditions
- Ergonomic, center balanced printer with grab and go ridged grip for easy handling
- Long life rechargeable battery allows printing on the go and decreases the need for frequent charging
- Prints up to 250 labels per day for higher volume printing

Designed to be easy

- Large LCD backlit display provides clear visibility
- QWERTY keypad, graphics library, hot keys and menu functions for fast label creation
- WYSIWYG functionality means you can see what you are printing – you'll only need to print once
- Magnet accessory for hands free printing

Engineered long lasting material quality

- Prints durable true-sized 25.4 mm wide identification to maximise amount of data on your label
- Take pride in your work with die-cut materials that make your job look uniform and professional or use a continuous material if you need to adjust the length of the label
- Fulfill your requirements with up to 10 different industry specified materials that last

Advanced all-in-one cartridge system

- Smart Cell Technology means your label format is automatically set up with no calibration
- Correct ribbon match for optimal print permanence
- Easy storage, transport and use of multiple cartridges
- Quick and easy to change supplies, just pop in the needed cartridge
- Pull tab on cartridge allows for one handed removal when changing supplies



Prints for a variety of applications. Key applications include wire marking, sleeving, panel labelling, terminal block, patch panel, general identification and more!

Printer Part Numbers

Article No.	Order Reference	Description
133254	BMP41-KIT-EU	BMP41 EU Label Printer
711213	BMP41-KIT-UK	BMP41 UK Label Printer
711214	BMP41-KIT-EU-LM	BMP41 EU Label Printer with LabelMark
711215	BMP41-KIT-UK-LM	BMP41 UK Label Printer with LabelMark
711216	BMP41-KIT-EU-LM-HC	BMP41 EU Label Printer with LabelMark and Hard Case
711217	BMP41-KIT-UK-LM-HC	BMP41 UK Label Printer with LabelMark and Hard Case

Printer Kit supplied with Nickel Battery Pack, MC1-1000-595-WT-BK cartridge, USB cable, AC adapter, Power Cord, Product CD, Brady Printer Drivers CD and Quick Start Guide. LabelMark Software Optional.



Printer Technical Data

The BMP™41 Label Printer is a rugged, portable solution that gives you the versatility to create die-cut or continuous labels up to 25 mm wide, anywhere, anytime! Whether you are faced with your jobs for the day or one-off tasks, the BMP™41 printer is the one device for all of your labelling jobs - from wire marking and general ID to multi-area labels such as patch panel or terminal block and more.

Print it once, print it all, get it done!

Specifications	
Print Technology	Thermal Transfer
Print Resolution (dpi)	300 dpi
Print Speed (mm/sec)	33 mm/second
Colour Capability	Monocolour
Continuous vs Die-cut Labels	Continuous Tape & Die Cut Labels
Max. Label Width	25.40 mm
Max. Print Length	990 mm
Recommended Usage/ Labels per Day	250
Stand-alone Printing (Detached from PC)	Yes
Connectivity Options	USB
PC Connectivity	Yes
Printing Modes	Wire Wrap, Terminal Block, Patch Panel, Flags, General, 66-Block, 110-Block, DesiStrip
Printing Functions	Print Preview, Serialisation, Date/Time Stamp, Fixed Length, Mirror, Vertical, Rotate, Auto Format, Multi-copy, Banner, Frame Feature
Bar Code Capability	Code 39 & UCC 128 Stand-alone, additional via software
Built-in Symbols	445
Software Compatibility	LabelMark
Physical Properties	
Depth x Height x Width	90 mm x 290 mm x 150 mm
Weight (kg)	1.3
Keyboard	QWERTY
Display	Large backlit screen
Cutter	Standard, Built-in, Manual
Warranty	2 years



WHEN PERFORMANCE MATTERS MOST™

Brady EMEA Locations

Africa	+27 11 704 3295	Middle East	+971 4881 2524
Benelux	+32 (0) 52 45 78 11	Norway	+47 70 13 40 00
Central & Eastern Europe	+421 2 3300 4800	Romania	+40 21 202 3032
Denmark	+45 66 14 44 00	Russia	+7 495 225 93 62
France	+33 (0) 3 20 76 94 48	Spain & Portugal	+34 900 902 993
Germany	+49 (0) 6103 7598 660	Sweden	+46 (0) 8 590 057 30
Hungary	+36 23 500 275	Turkey	+90 212 264 02 20
Italy	+39 02 26 00 00 22	UK & Ireland	+44 (0) 1295 228 288



Brady's LabelMark™ Labelling Software lets you easily design, edit and print labels for Asset ID, Component Marking, Telecom/ Datacom Labelling, Wiremarkers and more. Integrates completely with Microsoft® Office, Autocad® applications and more. You can download more detailed information on our LabelMark Labelling Software on www.bradyeurope.com.

Electrical Kit

Article No.	Order Reference	Description
711218	BMP41-KIT-EU-ELEC	BMP41 EU Label Printer Electrical Kit
711219	BMP41-KIT-UK-ELEC	BMP41 UK Label Printer Electrical Kit

Kit includes one of each

BMP41 EU Label Printer **or** BMP41 UK Label Printer

BMP41-HC BMP41 Hard Case

BMP41-MAGNET BMP41 Magnet

LM5 Std LabelMark 5 Standard Labelling Software

M-91-427 Black on White/Transparent Self-laminating Vinyl, 25.40 mm x 38.10 mm, 180 labels / Cartridge

MC1-1000-595-WT-BK Black on White Vinyl, 25.40 mm x 7.62 m, 1 / Cartridge

M-131-499 Black on White Nylon Cloth, 12.70 mm x 25.40 mm, 180 labels / Cartridge

Voice & Datacom Kit

Article No.	Order Reference	Description
711220	BMP41-KIT-EU-DATA	BMP41 EU Label Printer Voice & Data Kit
711221	BMP41-KIT-UK-DATA	BMP41 UK Label Printer Voice & Data Kit

Kit includes one of each

BMP41 EU Label Printer **or** BMP41 UK Label Printer

BMP41-HC BMP41 Hard Case

BMP41-MAGNET BMP41 Magnet

LM5 Std LabelMark 5 Standard Labelling Software

M-48-427 Black on White/Transparent Self-laminating Vinyl, 25.40 mm x 19.05 mm, 200 labels / Cartridge

MC1-1000-595-WT-BK Black on White Vinyl, 25.40 mm x 7.62 m, 1 / Cartridge

MC-375-422 Black on White Polyester, 9.53 mm x 7.62 m, 1 / Cartridge

Your Brady Distributor

20/08/2013
EUR-M-428-EN



Y3360504