

10/16 A German standard plugs and extensions

250 V~ - 19 mm centres



Pack	Cat.Nos	2 P+⊥ plastic - 10/16 A automatic cable grip
20/200	502 53	For round cable up to 2.5 mm ² (max Ø11 mm) Pin Ø4.8 Straight outlet plug
20/200	502 54	Side outlet plug

Pack	Cat.Nos	2 P+⊥ plastic - 10/16 A screw type cable grip
100	503 18	For round cable up to 2.5 mm ² (max Ø11 mm) Pin Ø4.8 Round plugs
100	503 19	Beige - straight outlet
20	513 74	Grey - straight outlet
20	513 77	Black - straight outlet
20	513 77	Black - side outlet
50	6501 05	White - straight outlet
100	513 50	Flat plugs
100	513 51	Beige
100	513 52	White
100	513 52	Grey
40	503 04	Extensions
40	503 08	Beige
10	502 63	Grey
10	502 63	White
20	503 03	French - German standard
20	503 03	White - side outlet
20	503 03	White - side outlet plug (NF - VDE - CEBEC - ONE)
10	502 85	Plug equipped with easy extraction rings (NF - KENA - CEBEC) for round cable up to 1.5 mm ²

Pack	Cat.Nos	2 P+⊥ - rubber - 10/16 A screw type cable grip
40	503 21	For round cable up to 2.5 mm ² (max Ø 12.5 mm) Plugs
10	502 52	Plug with waterproof covers (IP 44) - (KENA - OVE - VDE)
10	502 52	French-German standard plug White extraction handle (NF - VDE - CEBEC - KEMA - OVE)
30	513 64	Extensions
25	513 68	IP 40 - without cover VDE - OVE - AENOR
5	513 66	IP 44 - with waterproof cover VDE - OVE - AENOR
5	513 69	IP 44 - with closed cover
5	513 69	IP 44 - with inserted plug