

Part Number [↔](#)

FFS.00.250.NTCE31

Status Active

Size/Series 00 / 00

[Request a quote](#)

MECHANICAL DETAILS

Shell Style/Model FFS*: Straight plug with cable crimping
Keying Circular (can rotate)
Housing Material Brass (nickel plated) shell, collet nut, latch sleeve and mid pieces
Cable Fixing E31: 0 - 3 mm
Variant :

	A	L	M
mm.	6.4	31	23
in.	0.25	1.22	0.91

PERFORMANCE DETAILS

Insert Configuration 0.25 : 1 Coax (50 Ohm)
Insulator T: PTFE
Specifications
Contact Type: Coaxial 50 Ohm (Crimp)
Max. Matings: 5000
Contact Retention: 18 N
Contact Dia.: 0.7 mm (0.028in)
Bucket Dia.: 0.6 mm (0.024in)
R (max): 6.1 mOhm
Vtest: 2100 V (AC), 3000 V (DC)
Rated Current: 4 A (AC/DC)
Impedance: 50 Ohm
VSWR: 1.09 + 0.11 * f/GHz
Cable type: Storm 421-099

OTHER CHARACTERISTICS

Endurance (Shell) 5000 mating cycles
F ret (min): 100 N
IP Rating 50
Catalog

