

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300060194](#)
Status: **Active**
Overview: [Brad Mini-Change Connectors](#)
Description: Mini-Change A-Size Single-Ended Cordset, 2 Poles, Male (90°) to Pigtail, 16 AWG, PVC Cable, 1.83m (6.0') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
UL E152210

General

Product Family Industrial Cordsets
Series [130006](#)
Connector End A Mini-Change
Connector End B Pigtail
IP Rating IP67
Material - Contact Copper Alloy
Overview [Brad Mini-Change Connectors](#)
Product Name Mini-Change
Protocol N/A
Region America
Type Single Ended
UPC 78678842974

Physical

Cable Diameter 9.40mm (.370")
Cable Length 1.83m (6.0')
Color - Cable Jacket Yellow
Coupling Style Threaded
Gender Male-Pigtail
Keyway Single
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body PVC
Material - Coupling Nut Black Epoxy Coated Zinc
Material - Plating Mating Gold
Orientation 90° to Pigtail
Poles 2
Temperature Range - Operating -20°C to +105°C
Wire Size AWG 16
Wire/Cable Type ST00W

Electrical

Current - Maximum per Contact 13.0A
Voltage - Maximum 600V

Material Info

Engineering Number 102003A01F060

Reference - Drawing Numbers

Sales Drawing 1300060192-000, SD-130006-035-001



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130006](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION