



Part Number: 73660-0000

Image not available

Status: Active - Custom
Series: [73660](#)
Category: Backplane Connectors
Overview: [HDM®](#)

Series image - Reference only

Mates With Part(s):

[73644](#) HDM® Board-to-Board Backplane Header
[73799](#) HDM® Board-to-Board Duckpin Midplane Header

Product Environmental Compliance

[EU RoHS:](#) Compliance Status Not Reviewed
[China RoHS:](#)
[REACH SVHC:](#) Not Reviewed
[Low-Halogen Status:](#) Not Reviewed

Part Detail

General

Status	Active - Custom
Category	Backplane Connectors
Series	73660
Application	Daughtercard
Comments	Key Direction A
Component Type	Guide
Overview	HDM®
Product Name	HDM®
Style	N/A

Physical

Circuits (Loaded)	N/A
Circuits (maximum)	6
Color - Resin	Black
Durability (mating cycles max)	250
First Mate / Last Break	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Material - Metal	Stainless Steel
Material - Plating Mating	n/a
Material - Resin	High Temperature Thermoplastic
Number of Columns	N/A
Number of Pairs	Open Pin Field
Number of Rows	6
Orientation	Right Angle
PC Tail Length	N/A
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tube
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55°C to +105°C

Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	1A
Data Rate	N/A
Real Signals (per 25mm)	75
Shielded	No
Voltage - Maximum	250V

Material Info

UPC	800755024869
-----	--------------

Reference - Drawing Numbers

Sales Drawing	SDA-73660-****
---------------	----------------

Application Tooling

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)