




NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. CONTACT RATING: 50mA @12VDC
5. TRAVEL: 0.25 +0.2/-0.1mm
6. CONTACT RESISTANCE: 100mILLI-OHMS Max.
7. OPERATING FORCE: 160±50gf
- ▲8. CONTACT MATERIAL: SILVER
- 9.▲ DENOTES CRITICAL PARAMETER.
- ▲10. ACTUATOR: TOP (6.15MM), BOTTOM (11.85)
- ▲11. PACKAGE: TRAY/ 200 PIECES PER
12. 2002/95/EC (ROHS) COMPLIANT

RECOMMENDED P.C.B. LAYOUT

12. 2002/95/EC (ROHS) COMPLIANT				
B	19576	DRAWING UPDATE / CLEAN-UP	1/11/11	BGL
A	17000	RELEASED FOR PRODUCTION	2/20/07	TN
REV	PCR NO	DESCRIPTION	DATE	BY
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				
SCALE 2:1 DATE 2/20/2007 DR TN DWG P010686 REV B TITLE TL53HCF160Q E-SWITCH®				