




THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.
© 2003, Projects Unlimited Inc.

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED INPUT POWER	0.1	W
MAX INPUT POWER	0.3	W
IMPEDANCE	100±15%	OHM
OUTPUT SPL @ 1.0kHz/1M (AT 1.0 kHz)	76	dB
DISTORTION	5%	—
RESONANT FREQUENCY	1,000±200	Hz
FREQUENCY RANGE	1,000 ~ 10,000	Hz
HOUSING MATERIAL	NYLON	—
CONE MATERIAL	PET	—
MAGNET MATERIAL	ALNICO	—
OPERATING TEMPERATURE	-50 ~ +70	°C
WEIGHT	25	grams

REVISIONS

LTR	DESCRIPTION	DATE	APPROVED
—	RELEASED FROM ENGINEERING	5/13/02	
A	REVISED TO NEW TEMPLATE	4/15/04	R. W.



NOTES:

- ALL DIMENSIONS ARE IN MILLIMETERS.
- SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.

FILE NAME
AT-262.DWG

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN MILLIMETERS,
TOLERANCES ARE ±0.5 AND ANGLES ARE
±3°.

APPROVALS
DRAWN *RABL* 5/02
APPROVED *S.J.* 5/02

DO NOT SCALE DRAWING



projects®
unlimited

Dayton , Ohio

SPEAKER TRANSDUCER
AT-262

SIZE
A

DRAWING NO.
AT-262

SCALE: N.T.S.

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AT-262](#)