


THROUGH BOARD MOUNT




- Note: End stackable.
- Series 540 PLCC sockets are designed to accept JEDEC type MS-016 & MS-018 leaded plastic substrates.
- Body has polarizing features for both substrate and socket insertion.
- Contacts of highly reliable design safely hold the substrate in place by positive spring action.
- PLCC chip extraction tool available. See page 96.



PRINTED CIRCUIT DRILLING PATTERNS (TOP VIEW)

.030" dia. min. mounting holes



No. of Pins	ORDERING INFORMATION	- A -	- B -	- C -	- D -	Quantity per Tube
20	540-99-020-24-000	.590	.360	.200	.400	41
28	540-99-028-24-000	.690	.460	.300	.500	35
32*	540-99-032-24-000	.783 / .683	.564 / .464	.400 / .300	.600 / .500	24
44	540-99-044-24-000	.890	.660	.500	.700	27
52	540-99-052-24-000	.990	.760	.600	.800	24
68	540-99-068-24-000	1.190	.960	.800	1.000	20
84	540-99-084-24-000	1.390	1.160	1.000	1.200	17

*RECTANGULAR

ALL SERIES 540 CONTACTS ARE PLATED TIN/LEAD. SEE PAGE 96 FOR TECHNICAL SPECIFICATIONS.