

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0524190810](#)
Status: **Obsolete**
Description: 2.50mm (.098") Pitch Board-to-Board Receptacle, 8 Circuits

Documents:

General

Product Family	PCB Receptacles
Series	52419
Application	Board-to-Board, Signal

Physical

Circuits (Loaded)	8
Glow-Wire Compliant	No
Guide to Mating Part	Yes
Lock to Mating Part	Yes
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.20mm (.126")
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	3.20mm (.126")
Packaging Type	Tray
Pitch - Mating Interface	2.50mm (.098")
Polarized to PCB	No
Temperature Range - Operating	-40°C to +105°C


Electrical

Current - Maximum per Contact	2A
Voltage - Maximum	250V

Material Info

Reference - Drawing Numbers

Product Specification	PS-52419-001, PS-52419-002, RPS-52419-001, RPS-52419-002, RPS-52419-003
Sales Drawing	SD-52419-**10



EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[52419Series](#)

Mates With

[53291](#)