


## Dura Torsion Insert and Power Bits

With the Dura bit Wiha has again proved it's power of innovation. The extra hard, elastic Quattro Torsion bit is equipped with an extremely wear resistant tungsten carbide coating that grips the screw head.

Torsion  
Zone

**Positive location in the screw head with decrease of:**

- necessary pressure forces
- working time
- costs
- wear & tear of bits & screw heads
- anti-cam-out effect

## Carbide Coated



## 711 Dura Bits, Phillips, 1/4"

| Item No. | Size | mm | lbs. | Each Bit |
|----------|------|----|------|----------|
| 711 11   | 1    | 25 | .02  | \$4.66   |
| 711 12   | 2    | 25 | .02  | \$4.66   |
| 711 13   | 3    | 25 | .02  | \$4.66   |



## 712 Dura Bits, Pozidriv, 1/4"

| Item No. | Size | mm | lbs. | Each Bit |
|----------|------|----|------|----------|
| 712 11   | 1    | 25 | .02  | \$4.52   |
| 712 12   | 2    | 25 | .02  | \$4.52   |
| 712 13   | 3    | 25 | .02  | \$4.52   |



## 741 Dura Phillips Power Bits. 1/4" Hex Drive, Length 2.0"/50mm

| Item No. | Size | mm | lbs. | Each Bit |
|----------|------|----|------|----------|
| 741 41   | 1    | 50 | .04  | \$6.34   |
| 741 42   | 2    | 50 | .04  | \$6.34   |
| 741 43   | 3    | 50 | .04  | \$6.34   |



## 742 Dura Pozidriv Power Bits. 1/4" Hex Drive, Length 2.0"/50mm

| Item No. | Size | mm | lbs. | Each Bit |
|----------|------|----|------|----------|
| 742 41   | 1    | 50 | .04  | \$6.16   |
| 742 42   | 2    | 50 | .04  | \$6.16   |
| 742 43   | 3    | 50 | .04  | \$6.16   |



## 710 Dura Bits, Slotted, 1/4"

| Item No. | mm  | Inch | mm  | Inch | mm | Each Bit |
|----------|-----|------|-----|------|----|----------|
| 710 10   | 0.6 | .024 | 4.5 | .177 | 25 | \$5.48   |
| 710 11   | 0.8 | .030 | 5.5 | .216 | 25 | \$5.48   |
| 710 12   | 1.0 | .039 | 5.5 | .216 | 25 | \$5.48   |
| 710 13   | 1.2 | .039 | 6.5 | .255 | 25 | \$5.48   |



## 715 Dura Bits, TORX, 1/4"

| Item No. | Size | mm | lbs. | Each Bit |
|----------|------|----|------|----------|
| 715 74   | T10  | 25 | .02  | \$7.12   |
| 715 76   | T15  | 25 | .02  | \$7.12   |
| 715 78   | T20  | 25 | .02  | \$7.12   |
| 715 80   | T25  | 25 | .02  | \$7.12   |
| 715 82   | T30  | 25 | .02  | \$7.12   |
| 715 84   | T40  | 25 | .03  | \$7.12   |

## Diamond Torsion Insert and Power Bits

Diamond bits supplement Wiha's range of high-quality special bits. When used with machines, the increased tool life of the Wiha Diamond bit reduces cost.

Torsion  
Zone

- High wear resistance
- Micro particle coating with sapphire and diamond contents
- Optimized torsion zone

**Reduction of:**

- pressure forces to be applied
- wear and tear of bit and screw head
- working time
- working costs
- Cam-out effect

*The ideal bit even for the most difficult of applications*



## 710 Diamond Bits, Slotted, 1/4"

| Item No. | mm  | Inch | mm  | Inch | mm | Each Bit |
|----------|-----|------|-----|------|----|----------|
| 710 20   | 4.5 | .177 | 0.6 | .024 | 25 | \$5.16   |
| 710 21   | 5.5 | .216 | 0.8 | .030 | 25 | \$5.16   |
| 710 22   | 5.5 | .216 | 1.0 | .039 | 25 | \$5.16   |
| 710 23   | 6.5 | .255 | 1.2 | .039 | 25 | \$5.16   |
| 710 24   | 8.0 | .315 | 1.2 | .063 | 25 | \$5.16   |



## 711 Diamond Bits, Phillips, 1/4"

| Item No. | Size | mm | lbs. | Each Bit |
|----------|------|----|------|----------|
| 711 81   | 1    | 25 | .02  | \$4.48   |
| 711 82   | 2    | 25 | .02  | \$4.48   |
| 711 83   | 3    | 25 | .02  | \$4.48   |



## 712 Diamond Bits, Pozidriv, 1/4"

| Item No. | Size | mm | lbs. | Each Bit |
|----------|------|----|------|----------|
| 712 21   | 1    | 25 | .02  | \$4.36   |
| 712 22   | 2    | 25 | .02  | \$4.36   |
| 712 23   | 3    | 25 | .02  | \$4.36   |

## Diamond Coated



## 715 Diamond Bits, TORX, 1/4"

| Item No. | Size | mm | lbs. | Each Bit |
|----------|------|----|------|----------|
| 715 16   | T10  | 25 | .02  | \$6.54   |
| 715 17   | T15  | 25 | .02  | \$6.54   |
| 715 18   | T20  | 25 | .02  | \$6.54   |
| 715 19   | T25  | 25 | .02  | \$6.54   |
| 715 21   | T30  | 25 | .02  | \$6.54   |
| 715 22   | T40  | 25 | .03  | \$6.54   |



## 741 Diamond Phillips Power Bits. 1/4" Hex Drive, Length 2.0"/50mm

| Item No. | Size | mm | lbs. | Each Bit |
|----------|------|----|------|----------|
| 741 61   | 1    | 50 | .03  | \$5.98   |
| 741 62   | 2    | 50 | .03  | \$5.98   |
| 741 63   | 3    | 50 | .04  | \$5.98   |