




Honeywell
MICRO

SWITCH - BASIC

91SEI SERIES
CHART 1.



NOTE:

- 1 - MOUNTING HOLES WILL ACCEPT .087 MAX. (2.20) DIA. PINS OR SCREWS ON .375 ±.002 (9.53) CENTRES.
- 2 - ACTUATION IN LINE WITH ARROW "A" IS RECOMMENDED.
- 3 - WEIGHT OF SWITCH ONLY IS .26 OZ. (7.37) GRAMMES. WEIGHT PER FOOT OF SINGLE CONDUCTOR - SEE CHART.
- 4 - FLAT WITHIN .006 (0,15)
- 5 - METRIC DIMENSIONS IN BRACKETS ARE IN MILLIMETERS.
- 6 - METRIC WEIGHTS IN BRACKETS ARE GRAMMES.

NOTE	CATALOGUE LISTING	REL. No.	ISSUE	DIMENSION 'L' MINIMUM	WIRE LEADS	WEIGHT PER FOOT OF SINGLE CONDUCTOR
	91SEI	MS-1455	9	12.00 (304,80)	PT.FE. TO EL 1930 TYPE 'B' No. 20 (19 X .0076)	.11 OZS (3.12 GMS)
	91SEI-3	MS-1455	9	36.0 (914,40)	PT.FE. TO EL 1930 TYPE 'B' No. 20 (19 X .0076)	.11 OZS (3.12 GMS)
	91SEI-6	MS-1455	9	72.0 (1828,80)	PT.FE. TO EL 1930 TYPE 'B' No. 20 (19 X .0076)	.11 OZS (3.12 GMS)
	91SEI-4	MS-10055	5	48.0 (1219,20)	PT.FE. TO EL 1930 Type 'B' No. 20 (19 x .0076)	.11 oz. (3.12 gms.)
	91SEI-12	MS-2050	9	144.0 (3657,60)	PT.FE. TO EL 1930 TYPE 'B' No. 20 (19 X .0076)	.11 OZS (3.12 GMS)
4	91SEI-3N62	MS-10059	6	36.0 (914.40)	PTFE. to EL 1930 Type 'B' No. 20 (19 x .0076)	.11 oz. (3.12 gms.)

CHARACTERIST.	BRITISH	METRIC	ELECTRICAL DATA
OPERATING FORCE	5-17 OZS	141.75 - 487.95 GMS	CONTACT ARRANGEMENT S.P.D.T. BREAK DISTANCE .010 MIN. (.25)
RELEASE FORCE	4 OZ MIN.	113.40 GMS	250 VAC 30 VOLTS D.C. RATING
RELEASE TRAVEL	.004 MIN.	.10	INDUCTIVE SEA LEVEL 3 AMP 70,000 FT. 2.5 AMP
DIFFERENTIAL TRAVEL	.004 MAX.	.10	RESISTIVE SEA LEVEL 5 AMP 70,000 FT. 5 AMP
OVERTRAVEL	.003 MIN.	.07	MAXIMUM INRUSH 24 AMP

HONEYWELL LIMITED, Bracknell, Berks., & Newhouse, Lanarkshire.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[91SE1](#)