



OGA DIAGONAL: 31.48 [799.7]
VA DIAGONAL: 30.09 [764.4]
PA DIAGONAL: 28.37 [720.5]


US NUMBER	TYPE	DIM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PROD SPEC
98-0003-3481-7	FFC	8.00" [203.20]	AG500	23655
98-0003-3480-9	SER	8.00" [203.20]	AG500	23655
98-0003-3479-1	USB-R	8.00" [203.20]	AG500	23655



ESD CLAMPSHELL
CASE IS USED WITH ALL
NOV, USB AND SER
TERMINATIONS.

(USB-R)
EXII-7769UC
98-0003-2815-7
USB CONTROLLER
SOLDER SIDE

(SER)
EXII-7720SC
98-0003-2217-6
SERIAL CONTROLLER
SOLDER SIDE



1.47±.020 [3.73±.51]
TOTAL THICKNESS
OF GLASS, CABLE
AND STRAIN RELIEF

NOTES:

1. WEIGHT OF GLASS IN GRAMS: 2214±10%
2. NICOMATIC HOUSING P/N: OLOS
3. NICOMATIC RECEPTACLES (PINS) MATTE TIN PLATED P/N: 14106-12
4. HOUSING ORIENTED WITH LATCH DOWN

PINOUT	
1	LR
2	LL
3	SHLD
4	UL
5	UR

UNITS	INCHES [MM]
TOLERANCES UNLESS OTHERWISE SPECIFIED	
X	± .03 [1.76]
.XX	± .015 [1.38]
.XXX	± .01 [1.38]
ANGLES	± 1°

3M TOUCH SYSTEMS
3M TOUCH, MA
USA
THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE
3M COMPANY. NO PART OF THIS DOCUMENT MAY BE
REPRODUCED OR TRANSMITTED IN ANY FORM OR BY
ANY MEANS, ELECTRONIC OR MECHANICAL, WITHOUT
PERMISSION IN WRITING FROM THE 3M COMPANY.

REV	DESCRIPTION	DATE	BY
B	REVISED PER CO 034264	2/12	SB
01	RELEASE PER CO 030786	8/09	AH

MARKETING DRAWING
SCT32NN 30.09" W

DO NOT SCALE DRAWING	SCALE	1 = 1
DO NOT SCALE DRAWING	SCALE	1 = 1

37298-MKT