


Maximum Electric Rating: 600V
 Maximum Electric Current
 22-16AWG/0.5-1.5mm²: 19A
 16-14AWG/1.5-2.5mm²: 27A
 12-10AWG/4-6mm²: 48A
 Shrinking Temperature: ≥150°C
 Operating Temperature: -40°C ~120°C
 Shrinking Ratio: 3:1
 Terminal Body: Copper
 Insulation: PE
 Plating: Tin



Wire Range mm ² /AWG	Item No.	Stud Size		Dimension (mm)				Insulation Color
		Stud	d2	W	L	D	d1	
0.5~1.5mm ²	321043SSEL	#8	4.2	6.5	29.5	4.5	1.7	Red
22-16AWG	321053SSEL	#10	5.2	8	28			
1.5~2.5mm ²	325043SSEL	#8	4.2	6.4	32	5.2	2.3	Blue
16-14AWG	325053SSEL	#10	5.2	8.2	32			
4~6mm ²	323043SSEL	#8	4.2	8.4	38.7	7	3.5	Yellow
10-12AWG	323053SEL	#10	5.2	9	39.6			

Heat Shrink Spade connector