

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


Material	High Conductivity Seamless Copper Tube
Plating	Electro-Tin
Wire Size	2 STR/FLEX
Wire Type	Stranded Copper: Class B & C, Compact, Class G, H, I, K, M, Locomotive
Wire Strip Length	1-7/16 in.
Stud Size	3/8 in.
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
UL Temperature Rating	90° C
C.S.A Certified Wire Connector	Yes
Panduit Color Code on Barrel	BROWN
Panduit Die Index No. on Barrel	P33
Alternate Industry Die Index No. ( ) on Barrel	(10)



CERTIFIED



LISTED  
Wire Connector



REV	DATE	BY	CHK	RELEASED	ECN	SCALE	DRAWING NO / CAD FILE
00	6/03	SAC	SAC		10850	N/A	LCCX2-38DH-CUST
				DESCRIPTION			

**PANDUIT** CORP. TINLEY PARK, ILLINOIS

LCCX2-38DH-E  
Copper Lug - Two-Hole, Long Flex Barrel with Window, 45° Angle Tongue