


Rating		16(4)A 250V AC	   US	Mounting Hole	Circuit
Contact Resistance	50m ohm Max.				
Insulation Resistance	DC 500V 100M ohm Min.				
Dielectric Strength	AC 1500V 1 minute				
Switch Function	4P DPST ON - (OFF)				
Operation Temp.	0° C ~ 85° C				

GTS448Q301AHR