up to IP65 | NEMA | EN 45545-2 | NF F 16-101 | RoHS compliant | Made in Germany

KT

Inserts, small



1

Product description

Cable inserts KT small are used with the following cable entry frames:

- KEL(-ER) | Page 6 - 18
- KEL-FG | Page 20 - 21
- KEL-FL | Page 36
- KVT range | Page 22 - 28

The model range KT small is designed for cable diameters from 2 to 17 mm.

Assembly

When installing the insert, the smooth side of the insert faces the middle of the cable entry frame.

☐ Specification KT grey

Material	**Elastomer**
Flame class	**UL94-V0, self-extinguishing**
Temperature	**- 40°C to+ 90°C (static)**
Properties	**Halogen free, silicone free**

■ Specification KT black

Material	**Elastomer**
Flame class	**UL94-HB**
Temperature	**- 30°C to + 90°C (static)**
Properties	**Higher chemical resistance, UV-stabilised**

Accessories

ST Plugs Page 35

Description		Type	Order No grey	Order No black	Clamping range	PU
BTK		BTK	☐ 41251	■ 41351	Blind insert	10
KT		KT 2	☐ 39934	■ 41302	2 - 3 mm	10
		KT 3	☐ 41203	■ 41303	3 - 4 mm	10
		KT 4	☐ 41204	■ 41304	4 - 5 mm	10
		KT 5	☐ 41205	■ 41305	5 - 6 mm	10
		KT 6	☐ 41206	■ 41306	6 - 7 mm	10
		KT 7	☐ 41207	■ 41307	7 - 8 mm	10
		KT 8	☐ 41208	■ 41308	8 - 9 mm	10
		KT 9	☐ 41209	■ 41309	9 - 10 mm	10
		KT 10	☐ 41210	■ 41310	10 - 11 mm	10
		KT 11	☐ 41211	■ 41311	11 - 12 mm	10
		KT 12	☐ 41212	■ 41312	12 - 13 mm	10
		KT 13	☐ 41213	■ 41313	13 - 14 mm	10
		KT 14	☐ 41214	■ 41314	14 - 15 mm	10
		KT 15	☐ 41215	■ 41315	15 - 16 mm	10
KT oval		KTs 16	☐ 39901	■ 39912	16 mm	10
		KTs 17	☐ 39900	■ 39913	17 mm	10
KT S1		KT oval	☐ 39930	-	approx. 8 × 4 mm	10
KT tele		KT S1	☐ 39931	-		10
KT tele1		KT tele	☐ 39929	-	Telephone cable	10
		KT tele1	☐ 41257	-	Data cable RJ12	10
KT tele2		KT tele2	☐ 41258	-	Data cable RJ10 / RJ45	10

*Only valid for grey product types

up to IP65 | NEMA | EN 45545-2* | NF F 16-101* | RoHS compliant | Made in Germany

KT
Inserts, small

Type	Order No grey	Order No black	Clamping range	PU	Description
KT 2|2	☐ 39935	■ 39936	2× ø 2 mm	10	
KT 2|3	☐ 39939	■ 39940	2× ø 3 mm	10	
KT 2|4	☐ 39906	■ 39907	2× ø 4 mm	10	
KT 2|5	☐ 41200	■ 39904	2× ø 5 mm	10	
KT 2|6	☐ 41201	■ 39905	2× ø 6 mm	10	
KT 2|7	☐ 41202	■ 39916	2× ø 7 mm	10	
KT 2|8	☐ 39917	■ 39918	2× ø 8 mm	10	
					KT 2|×
KT 4|2	☐ 39937	■ 39938	4× ø 2 mm	10	
KT 4|3	☐ 39914	■ 39915	4× ø 3 mm	10	
KT 4|4	☐ 39909	■ 39911	4× ø 4 mm	10	
KT 4|5	☐ 39908	■ 39910	4× ø 5 mm	10	
KT 4|6	☐ 39932	■ 39933	4× ø 6 mm	10	KT 4|×
					KT ASI2|rl
KT-ASI	☐ 39902	■ 39903	1 ASI-cable	10	
KT-ASI2|rl	☐ 39922	■ 39924	2 ASI-cables	10	
KT-ASI2|ll	☐ 39921	■ 39923	2 ASI-cables	10	KT ASI2|ll

*Only valid for grey product types

Product description

Cable inserts KT small are used with the following cable entry frames:

- KEL(-ER) | Page 6 - 18
- KEL-FG | Page 20 - 21
- KEL-FL | Page 36
- KVT range | Page 22 - 28

The model range KT small is designed for cable diameters from 2 to 17 mm.

Assembly

When installing the insert, the smooth side of the insert faces the middle of the cable entry frame.

☐ Specification KT grey

Material	**Elastomer**
Flame class	**UL94-V0, self-extinguishing**
Temperature	**- 40°C to+ 90°C (static)**
Properties	**Halogen free, silicone free**

■ Specification KT black

Material	**Elastomer**
Flame class	**UL94-HB**
Temperature	**- 30°C to + 90°C (static)**
Properties	**Higher chemical resistance, UV-stabilised**

Accessories

ST Plugs Page 35