


NEW**KE**

- 16mm mounting hole
- 10mm ultra-bright LED
- Supplied with nylon hex nut

SPECIFICATIONS

Body Material: Nylon 66 (UL 94V-2)
 Nut Material: Nylon 66 (UL 94V-2)
 Terminal Material: Nickel over Brass

Operating Temp: -20°C to +85°C
 Certifications: See Page 1



Series		Lamp		Termination		Base		Bezel		Lens			
XX		XX		- X		- X		X		- XXX X 0			
KE	Voltage	Type	Code	Style	Code	Color	Code	Finish	Code	Style	Code	Color	Code
	14	LED	12	.250 Tabs	4	N/A	0	Black	3	Translucent	010	Red	1
	28	LED	13							Water Clear ²	050	Amber	2
	125	LED ¹										Green	4
												Blue	5
												White	6
												Pure White	P

LED Viewing Angle 120°**LED Light Output (mcd)**

Red	250
Amber	200
Green	700
Blue	300
White	500
P White	4000

ADDITIONAL OPTIONS AVAILABLE:

Contact Factory

1. Contact Factory
2. Pure White Only