

FLK 34/EZ-DR/ 300/KONFEK

Order No.: 2299518

The illustration shows a 20-position version



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2299518>

Round cable set, with two 34-pos. socket strips (1:1 connection), cable length: 3 m

Commercial data

EAN	4017918886233
Pack	1 pcs.
Customs tariff	85444290
Weight/Piece	0.4345 KG
Catalog page information	Page 264 (IF-2009)

Product notes

WEEE/RoHS-compliant since:
03/13/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Nominal voltage U_N	< 50 V AC
	60 V DC
Max. current carrying capacity per path	1 A
Max. conductor resistance	0.16 Ω /m
Ambient temperature (operation)	-20 °C ... 50 °C

Ambient temperature (storage/transport)	-20 °C ... 70 °C
Number of positions	34
Number of positions, control side	34
Number of connectors, control side	1
Number of positions, module side	34
Number of connectors, modul side	1
Fixed cable length	3 m
Single wire, cross section	0.14 mm ²
AWG	26
Conductor construction: Number of litz wires:	7
Single wire, material	Cu tin-plated
External diameter	10 mm
Cable, preassembly	Insulation displacement, IEC 60352-4/DIN EN 60352-4
Shielding	no

Certificates / Approvals



Certification	GOST
Certifications applied for:	UL / CUL

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;