

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 50-57-9320
Status: Active
Overview: SL™ Modular Connectors
Description: SL™ Crimp Housing, Single Row, Version D, Back Ribs, 20 Circuits



Series

image - Reference only

Documents:

- 3D Model
- Drawing (PDF)
- Product Specification PS-70058 (PDF)
- Product Specification PS-70400 (PDF)
- Product Specification PS-71851 (PDF)
- Test Summary TS-70058-001 (PDF)
- RoHS Certificate of Compliance (PDF)

Agency Certification

CSA LR19980
UL E29179

General

Product Family Crimp Housings
Series 70066
Application Signal, Wire-to-Board
Comments Version D
Overview SL™ Modular Connectors
Product Name SL™
UPC 800753724914

Physical

Circuits (maximum) 20
Color - Resin Black
Flammability 94V-0
Gender Female
Glow-Wire Compliant No
Keying to Mating Part Yes
Lock to Mating Part No
Material - Resin Polyester Alloy
Net Weight 1.532/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 2.54mm
Stackable Yes
Temperature Range - Operating -40°C to +105°C

Electrical

Current - Maximum per Contact 3A

Material Info

Old Part Number 70066-0124

Reference - Drawing Numbers

Product Specification PS-70058, PS-70400, PS-71851
Sales Drawing SD-70066-0106-0129
Test Summary TS-70058-001

EU RoHS

ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

70066Series

Mates With

70004 Interim Clip, 70013 , 70022 , 70104 , 70475 , 70431 , 70543 , 70553

Use With

SL™ Crimp Terminal 70021 , 70058 , 71851