








6.1	37.7	20	6		2-173268-6	4-173268-6		8-173268-6
6.1	32.7	15	5		2- ↑ -5	4- ↑ -5		8- ↑ -5
6.3	27.6	10	4		2- ↑ -4	4- ↑ -4		8- ↑ -4
6.4	22.6	5	3		2- ↓ -3	4- ↓ -3		8- ↓ -3
6.6	17.5	—	2		2-173268-2	4-173268-2		8-173268-2
"T"	"E"	"N"	極数 Pos.		黒 BLACK	青 BLUE		赤 RED
色及び型番 : COLOR & P/N								

© 19 年 日本エー・エム・ピー株式会社
AMP社の諸製品は特許又は特許出願中

© 19 BY AMP (Japan) LTD.
ALL RIGHTS RESERVED. AMP
PRODUCTS COVERED BY PATENTS
AND OR PATENTS PENDING

日本エー・エム・ピー株式会社
TOKYO, JAPAN

包含電線断面積(WIRE RANGE)
mm²(AWG)

被覆外径 (INSULATION DIA.)
mm

名称 (NAME)

材料 (MATERIAL)
ポリプロピレンテレフタレート
P.B.T. (94V-0)

仕上 (FINISH)
—

一般公差

10以下 ± 0.2
10を超え 30以下 ± 0.25
30を超え 100以下 ± 0.3
角 度 ± 3°

SYZE LOC 番号 (NO.)

C J C-173268

尺度 (SCALE) REV. 0 SHEET

製品仕様書	PRODUCT SPEC.	108-5171
取付適用仕様書	APPLICATION SPEC.	114-5074
取扱説明書	INSTRUCTION SHEET	IS-202J

0	RELEASED J85-8/58	27	20	5/85
LTR	変更 (REVISION RECORD)	DR.	CHK.	DATE

DR.	J. Inai 5/10	DE.	
CHK.	J. Inai 5/10	APP.	J. Inai 5/10