




Product Data Sheet

Part No. PT-1404 Non-Washable Type


DIMENSIONS

PT-1404




$\phi 13.6 \times H4.0$

TOP VIEW



SIDE VIEW



Type	Unit	PT-1404
Rated Voltage Square Wave	(Vpp)	9
Operating Voltage	(Vpp)	1~30
Current Consumption	(mA)	< or = 3
Capacitance at 120 Hz	(pF)	10000±30%
Sound Output (Min)	(dB)	> or = 80
Resonant Frequency	(Hz)	4800±300
Operating Temp	(C)	-20~+60
Storage Temp	(C)	-20~+80
Weight	(g)	5
Dimension	mm	13.6 x H4
*Value applying at rated voltage		
*distance for measurement 10cm		

FREQUENCY RESPONSE

