




PANDUIT PART NO.	BUNDLE DIA MIN - MAX.	DIMENSIONS					MATERIAL	COLOR	WEIGHT grams 100 pcs
			'B'	'C'	'D'	'E'			
HCMU04C13-...20	4 - 13		5.7	10.0	26.7	19	NYLON 6/6	SCHWARZ black	180
HCMU04C13-...469							NYLON 4/6	NATUR natural	



SCALE: FULL

NOTES:

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, AND COLOR.
2. (*) DIMENSIONAL VARIANCE IS POSSIBLE DUE TO MOLDING PROCESS RELATED SINK MARKS.
3. APPLICATION SPECIFICATION:
HOLE DIAMETER: 6.3 - 6.6 mm
PANEL THICKNESS: 0.8 - 2.3 mm

CAD FILENAME/LAYERS		G01932BB_PB_HCMU04C13_07	
PANDUIT CORP. TINLEY PARK, ILLINOIS			
HARNESS CLIP WITH PUSH MOUNT ANCHOR AND UMBRELLA			
UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE METRIC TOLERANCE: ±0.5 mm			
DRAWN BY CGSM		MAT'L:	
DATE 2-17-98		SCALE 1.5X	
CHK'D		DRAWING NO. GB1932BB	
		DWG A SIZE	

7	3-3-06	TMSA		REVISED DIM "D" FROM 27.6	GB1932BB	7			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	