






W1G200EA Series

Axial

Ø 200mm Energy-Saving Motor (ESM)

- Energy saving AC axial fan with 2 pre-programmable speeds.
- All metal construction coated in galvanic dipping varnish.
- Mounting plate with 4.3 mm holes.
- Air exhaust over struts. Direction of rotation is CCW looking at rotor.
- Maintenance-free ball bearings.
- UL, CSA, VDE approvals on most models, please contact application engineering.

Part Number	Curve	CFM @ 0	VAC	Hertz	Power (W)	dBA	Max Amb. Temp C	Bearing Type	Speed (RPM)
W1G200-EA91-27	1	294	115	50/60	7	42	50	Ball	1400
W1G200-EA95-47	2	471	115	50/60	27	56	50	Ball	2200
W1G200-EA87-25	1	294	230	50/60	7	42	50	Ball	1400
W1G200-EA91-45	2	471	230	50/60	27	56	50	Ball	2200



ebmpapst

e-mail: sales@us.ebmpapst.com · TEL: 860-674-1515 · FAX: 860-674-8536

ebm-papst Inc., 100 Hyde Road, Farmington, CT 06034 USA

ebm-papst Inc., 2006 © ebm-papst Inc. reserves the right to change any specifications or data without notice

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ebm-papst:](#)

[W1G200-EA87-25](#) [W1G200-EA91-27](#) [W1G200-EA91-45](#) [W1G200-EA95-47](#)