



Current refinements (click  to remove)

[Search Tips](#) 

☐ Region USA ☐ Product Family HLT Loop Ties ☐ Text Search: 'HLT-215'

Your search criteria matched only one product, shown below.

Related Products

[Tak-Ty Hook & Loop Cable Tie...](#)

[Tak-Ty Hook & Loop Cable Ti...](#)

 [Click here to see ima](#)

- Broadest selection of sizes, styles, and colors to meet your application needs
- Adjustable, releasable, and reusable hundreds of times for applications requiring frequent moves, adds, or changes
- Hook and loop material maintains network data integrity by protecting against over-tensioning of high performance copper and fiber cables
- Easy to use and operator safe with no sharp edges

Note: Minimum 2" overlap required to achieve loop tensile rating

Part Number:	HLT21-X5
RoHS Compliancy Status:	Compliant
Part Description:	Hook & Loop Cable Tie, Loop Tie, 8.0", Intermediate cross section
Product Type:	Cable Ties
Material:	Nylon Loop, Polyethylene Hook
Color:	Green
CSA Certified:	No
UL Listed (File #E56854):	No
UL Recognized (File #E56854)	No
Length (In.):	8.0
Length (mm):	203
Width (In.):	.500
Width (mm):	12.7
CE Compliant:	Yes
Cross Section:	Intermediate
Locking Style:	Hook & Loop
Max. Bundle Diameter (In.):	1.91
Max. Bundle Diameter (mm):	49
Min. Loop Tensile Strength (Lb)	40
Min. Loop Tensile Strength (N)	178
Temperature Range:	0°F to 220°F
Thickness (In.):	.10
Thickness (mm):	2.5
Min. Order UOM:	PC
Min. Order Qty.:	10
BOM Qty. (# of Pkgs.)	0
Add to My Catalog	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features