



LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REVISED PER 0G3B-0204-05	23APR05	KW	CJ



1 MATERIAL: CONTACTS - BRASS
HOUSING - UL 94V-0 RATED HIGH TEMP NYLON, COLOR BLACK.

2 PLATING: CONTACTS - 2.54μm MINIMUM TIN-LEAD OVER 1.27μm MINIMUM NICKEL.

4 RECOMMENDED PC BOARD THICKNESS OF 1.57.

5 PLATING: CONTACTS - 2.54μm MINIMUM MATTE TIN OVER 1.27μm MINIMUM NICKEL.

	33.00	28.70	40.00	12	3-1445058-2
	30.00	25.70	37.00	11	3-1445058-1
	27.00	22.70	34.00	10	3-1445058-0
	24.00	19.70	31.00	9	2-1445058-9
	21.00	16.70	28.00	8	2-1445058-8
	18.00	13.70	25.00	7	2-1445058-7
	15.00	10.70	22.00	6	2-1445058-6
	12.00	7.70	19.00	5	2-1445058-5
	9.00	4.70	16.00	4	2-1445058-4
	-	-	13.00	3	2-1445058-3
	-	-	10.00	2	2-1445058-2
	33.00	28.70	40.00	12	1-1445058-2
	30.00	25.70	37.00	11	1-1445058-1
	27.00	22.70	34.00	10	1-1445058-0
	24.00	19.70	31.00	9	1445058-9
	21.00	16.70	28.00	8	1445058-8
	18.00	13.70	25.00	7	1445058-7
	15.00	10.70	22.00	6	1445058-6
	12.00	7.70	19.00	5	1445058-5
	9.00	4.70	16.00	4	1445058-4
	-	-	13.00	3	1445058-3
	-	-	10.00	2	1445058-2
FINISH	DIM Z	DIM V	DIM W	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN J.ROOT 020C12001 CHK K. WHITAKER 13-MAR-2001 APVD K. WHITAKER 13-MAR-2001		AMP Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RT ANGLE SURFACE MOUNT HEADER ASSY, TIN CONTACTS W/PLASTIC HOLDDOWNS, SINGLE ROW, MICRO MATE-N-LOK™	
		0 PLC ±.010 1 PLC ±.010 2 PLC ±.010 3 PLC ±.010 4 PLC ±.010 ANGLES ±.010		PRODUCT SPEC - APPLICATION SPEC -	
MATERIAL - 		FINISH SEE TABLE		SIZE A2 CAGE CODE 00779 DRAWING NO. C-1445058	
		WEIGHT -		SCALE 5:1 SHEET 1 OF 2 REV B	
		CUSTOMER DRAWING			

AMP 1471-9 REV 09MAY94

METRIC

