




Dimensions (Unit: mm)



Ordering Information

Part No.	Description
ACE-716C-RS	150 W 24 V DC Input AT Power Supply

Option 1	Embedded Solution	Option 2	AT P8P9 Backplane Solution
	PN: CB-716EB-RS 30 cm DC cable to CPU card with 4-pin 12 V CPU, HDD and SATA connectors		PN: CB-716P8P9-RS 30 cm DC cable AT power to P8P9 with HDD and SATA connectors




Specifications

Input Type	90~264 VAC Full Range	
Output Voltage	+12 V	+24 V
	15 A (1 A min.)	3 A (0 A min.), peak load 8 A
Efficiency	80%	
Temperature	Operating: 0°C ~ 50°C Storage: -20°C ~ 80°C	
MTBF (hrs)	100,000	
Output Connector	1 x 5-pin molex 39-01-2100 1 x 4-pin power mini-DIN for +12 VC 1 x 3-pin power mini-DIN for +24 VDC	
Dimensions (mm)	140 x 150 x 86	


Ordering Information

Part No.	Description
ACE-D825A-RS	252W Flex Power Supply
ACE-D825A-H-RS	252W Flex Power Supply, with rubber sleeve

Dimensions (Unit: mm)



■ Output Pin Definitions



Pin	1	2	3	4	5	6	7	8	9	10
	COM	COM	COM	COM	+24V +24V _{dc}	+12V +12V _{dc}	+12V	+12V	+12V	+24V