








USED ON													—	
TOOL NUMBER  -1 	WIRE SIZE mm ² [AWG] 	INSULATION DIAMETER mm [in.] 	INSUL. ADJ. 	FLIP LOCATOR 	STRIP LENGTH mm [in.] 	CRIMP HEIGHT mm [in.] 	CONTACT PART NUMBERS 						CONTACT DESCRIPTION (loose piece color code)	APPLIC. SPECIF.
							LOOSE PIECE 			STRIP FORM 				
91505-1	0.2 - 0.6 [24-20]	1.14 - 1.78 [.045-.070]	YES	NO	3.96 ± 0.38 [.156 ± .015]	1.01 ± 0.05 [.039 ± .002]	66103-[] 66400-[] 164163-[]	66105-[] 163086-[]	66399-[] 163088-[] 170246-[] 170248-[] 66702-[]	66102-[] 66332-[] 164160-[]	66104-[] 163085-[]	66331-[] 163087-[] 170245-[] 170247-[] 66671-[] 66672-[]	Type III+ (yellow)	114-10004
91505-3	0.8 - 1.4 [18-16]	2.03 - 2.54 [.080-.100]				1.30 ± 0.05 [.051 ± .002]	66099-[] 164164-[] 66589-[]	66101-[] 163082-[] 164839-[] 170244-[] 66590-[]	163084-[] 164840-[] 170242-[]	66098-[] 164161-[] 66579-[]	66100-[] 163081-[] 163766-[] 170243-[] 66580-[]	163083-[] 163767-[] 170241-[]	Type III+ (blue and violet)	Type VI
91515-1	0.05 - 0.38 [30-22]	1.02-1.91 [.040-.075]	NO	NO	3.50-4.75 [.140-.187]	0.79 ± 0.05 [.031 ± .002]	61173-[]	61174-[]		350078-[]	350079-[]	COMMERCIAL M-N-L	114-1012	
	66107-[] 163092-[] 66595-[]	66109-[] 164163-[] 66596-[]					163090-[] 170250-[] 170252-[]	66106-[] 163091-[] 66585-[]	66108-[] 164160-[] 66586-[]	163089-[] 170249-[] 170251-[]	Type III+ (red)	Type VI	114-10004 114-10007	
	91515-3	0.2 - 0.6 [24-20] 0.05 - 0.15 [30-26]				1.14-1.78 [.045-.070]	1.003 ± 0.051 [.0395 ± .002]	66103-[] 163088-[] 66428-[] 66593-[]	66105-[] 164162-[] 66429-[] 66594-[]	163086-[] 170246-[] 170248-[]	66102-[] 163087-[] 66424-[] 66583-[]	66104-[] 164159-[] 66425-[] 66584-[]	163085-[] 170245-[] 170247-[]	Type III+ (yellow & brown)
91519-1	0.8 - 1.4 [18-16]	2.03-2.54 [.080-.100]	YES	NO	3.96 ± 0.38 [.156 ± .015]	1.30 ± 0.05 [.051 ± .002]	66360-[] 66361-[]			66358-[] 66359-[]			Type III+	114-10004
91519-3	1.9 - 2.1 [14]					1.73 ± 0.05 [.068 ± .002]								
91521-1	0.8 - 1.4 [18-16]	2.79-3.81 [.110-.150]	YES	NO	4.75 ± 0.38 [.187 ± .015]	1.30 ± 0.05 [.051 ± .002]	66601-[] 66602-[]			66598-[] 66597-[]			Type III+	114-10004
91521-3	1.9 - 2.1 [14]					1.73 ± 0.05 [.068 ± .002]	213603-2 213603-4	213603-1 213603-3						
91523-1	0.2 - 0.6 [24-20]	2.03-2.54 [.080-.100]	NO	NO	3.56-4.75 [.140-.187]	0.99 ± 0.05 [.039 ± .002]	66400-[] 66399-[]			66332-[] 66331-[]			Type III+ (yellow)	114-10004
	91523-3					0.8 - 1.4 [18-16]	1.30 ± 0.05 .051 ± .002]	163082-[] 163084-[] 66589-[]	164164-[] 66099-[] 66590-[]	66101-[] 170242-[]	163081-[] 163083-[] 66579-[]	164161-[] 66098-[] 66580-[]	66100-[] 170241-[]	Type III+ (blue)
91542-1	0.2 - 0.35 [24-22]	1.52-3.43 [.060-.135]	YES	NO	3.96 ± 0.38 [.156 ± .015]	0.89 ± 0.08 [.035 ± .003]	66565-[] 66566-[]			66563-[] 66564-[]			Type III+ (yellow)	114-10004
91542-3	2X 0.2 OR 0.56 [2X 24 OR 20]					0.99 ± 0.08 [.039 ± .003]								
91550-1	0.8 - 1.4 [18-16]	2.03-3.43 [.080-.135]	YES	NO	4.75 ± 0.38 [.187 ± .015]	1.30 ± 0.05 [.051 ± .002]	66587-[] 66588-[]			66577-[] 66578-[]			Type VI	114-10007
91550-3	1.9 - 2.1 [14]					1.73 ± 0.05 [.068 ± .002]								


⚠ LIST OF APPLIED CONTACT PART NUMBERS
MAY NOT BE COMPLETE AND IS SUBJECT
TO CHANGE. FOR CURRENT INFORMATION
ON TERMINAL PART NUMBERS, CONTACT
THE TOOLING ASSISTANCE CENTER :
1-800-722-1111.

2. AMP and CERTI-CRIMP are trademarks.

△ -1 IS A CERTICRIMP II HAND TOOL ASSEMBLY.
-3 IS A CERTICRIMP II HEAD SUB-ASSEMBLY.

4. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414.

CERTI-CRIMP II DATA SHEET

										DWN		21FEB2012		MATERIAL		HEAT TREAT			
										M. YOUNGER				-		-			
										CHK		22FEB2012		 TE Connectivity					
										B.A.WOLFE									
										APVD		22FEB2012							
										B.A. WOLFE									
										NAME		CERTI-CRIMP II TOOL DATA SHEET							
												MULTIMATE CONTACT FAMILY OPEN BARREL							
										SCALE		SIZE		DRAWING NO.		SHEET		REV	
										-		A1		1583004		1		OF 2	
																		D1	










				DIMENSIONS:				TOLERANCES UNLESS OTHERWISE SPECIFIED:			
				mm							
											
				0 PLC				± -			
				1 PLC				± -			
				2 PLC				± -			
				3 PLC				± -			
				4 PLC				± -			
				ANGLES ±							
				SURFACE TEXTURE							

D1		REVISED		10/2017		AW		CM	
P	LTR	REVISION RECORD		DATE		DWN		APVD	

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY. IT IS THE PROPERTY OF TE CONNECTIVITY AND IS NOT TO BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TE CONNECTIVITY. ANY UNAUTHORIZED DISCLOSURE OR USE OF THIS INFORMATION IS PROHIBITED AND WILL BE SUBJECT TO LEGAL ACTION.

1583004

THIS DRAWING IS A CONTROLLED DOCUMENT.

USED ON												
TOOL NUMBER  -1 	WIRE SIZE mm ² [AWG] 	INSULATION DIAMETER mm [in.] 	INSUL. ADJ. 	FLIP LOCATOR 	STRIP LENGTH mm [in.] 	CRIMP HEIGHT mm [in.] 	CONTACT PART NUMBERS 				CONTACT DESCRIPTION (loose piece color code)	APPLIC. SPECIF.
							LOOSE PIECE 		STRIP FORM 			
91564-1 91564-3	0.20-0.56 [24-20]	1.02-2.03 [.040-.080]	NO	NO	3.55-4.75 [.140-.187]	1.00 ± 0.05 [.039 ± .002]	66103-[] 66593-[] 66596-[] 66105-[] 170246-[] 66594-[]	66102-[] 66583-[] 66586-[] 66104-[] 170245-[] 66584-[]	Type III+ (yellow)	114-10004		
	0.05-0.15 [30-26]	1.02-1.52 [.040-.060]					66429-[] 170248-[] 66595-[] 66428-[]	66425-[] 170247-[] 66585-[] 66424-[]				
	0.12-0.22 [26-24]	0.89-1.40 [.035-.055]					66107-[] 66237-[] 170252-[] 66109-[] 170250-[]	66106-[] 170249-[] 66108-[] 170251-[]	(red)			
2844982-1	0.30 [22]	1.27-2.79 [.050-.110]	NO	NO	4.37 [.172]	0.94 ± 0.05 [.037 ± .002]	66591-[]	66581-[]	TYPE VI INSULATION GRIP CONTACTS	114-10007		
	0.60-0.80 [20-18]	1.27-2.79 [.050-.110]					66592-[]	66582-[]				

1. LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.
2. AMP and CERTI-CRIMP are trademarks.
3. -1 IS A CERTICRIMP II HAND TOOL ASSEMBLY.
-3 IS A CERTICRIMP II HEAD SUB-ASSEMBLY.
4. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414.

CERTI-CRIMP II DATA SHEET

DWG: 21FEB2012		MATERIAL: -	HEAT TREAT: -
CHK: 22FEB2012		B.A. WOLFE	
APVD: 22FEB2012		B.A. WOLFE	
NAME: CERTI-CRIMP II TOOL DATA SHEET			
MULTIMATE CONTACT FAMILY OPEN BARREL			
SCALE: -	SIZE: A1	DRAWING NO: 1583004	SHEET 2 of 2
REV: D1			

P	LTR	REVISION RECORD	DATE	DWN	APVD
-	SEE SHEET 1	-	-	-	-

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0 PLC	± .	1 PLC	± .
1 PLC	± .	2 PLC	± .
2 PLC	± .	3 PLC	± .
3 PLC	± .	4 PLC	± .
ANGLES: ±		SURFACE TEXTURE: √	