



Adhesive Transfer Tapes with Adhesive 200MP

467MP • 468MP • 467MPF • 468MPF • 7952MP

7955MP • 7962MP • 7965MP • 9172MP • 9185MP

9667MP • 9668MP

Technical Data

March, 2014

Product Description

3M™ High Performance Acrylic Adhesive 200MP is a popular choice, and industry standard, for graphic attachment and general industrial joining applications. It provides outstanding adhesion to metal and high surface energy plastics. This adhesive provides some initial repositionability for placement accuracy when bonding to plastics. It also performs well after exposure to humidity and hot/cold cycles.

- Up to 400°F short-term heat resistance
- Excellent solvent resistance
- Excellent shear strength to resist slippage and edge lifting

Construction Information




Product	Adhesive Thickness mils (mm)	Liner Type Liner Thickness mils (mm)	Liner Color
467MP	2.3 mils (0.06 mm)	58# Polycoated Kraft Paper (PCK) 4.2 mils (0.11 mm)	
468MP	5.2 mils (0.13 mm)	58# Polycoated Kraft Paper (PCK) 4.2 mils (0.11 mm)	
467MPF	2.3 mils (0.06 mm)	Polyester Film (PET) 2.0 mils (0.05 mm)	
468MPF	5.2 mils (0.13 mm)	Polyester Film (PET) 2.0 mils (0.05 mm)	






3M™ Adhesive Transfer Tapes with Adhesive 200MP

467MP, 468MP, 467MPF, 468MPF, 7952MP, 7955MP, 7962MP, 7965MP, 9172MP, 9185MP, 9667MP, 9668MP

Construction Information (continued)

Product	Adhesive Thickness mils (mm)	Liner Type Liner Thickness mils (mm)	Liner Color
9667MP	2.3 mils (0.06 mm)	83# Polycoated Kraft Paper (PCK) 6.2 mils (0.16 mm)	
9668MP	5.2 mils (0.13 mm)	83# Polycoated Kraft Paper (PCK) 6.2 mils (0.16 mm)	



Product	Adhesive Thickness mils (mm)	Liner 1 Type Liner 1 Thickness mils (mm)	Liner 1 Color	Liner 2 Type Liner 2 Thickness mils (mm)	Liner 2 Color
7952MP	2.3 mils (0.06 mm)	58# Polycoated Kraft Paper (PCK) 4.2 mils (0.11 mm)		58# Polycoated Kraft Paper (PCK) 4.2 mils (0.11 mm)	
7955MP	5.2 mils (0.13 mm)	58# Polycoated Kraft Paper (PCK) 4.2 mils (0.11 mm)		58# Polycoated Kraft Paper (PCK) 4.2 mils (0.11 mm)	
7962MP	2.3 mils (0.06 mm)	83# Polycoated Kraft Paper (PCK) 6.2 mils (0.16 mm)		58# Polycoated Kraft Paper (PCK) 4.2 mils (0.11 mm)	
7965MP	5.2 mils (0.13 mm)	83# Polycoated Kraft Paper (PCK) 6.2 mils (0.16 mm)		58# Polycoated Kraft Paper (PCK) 4.2 mils (0.11 mm)	
9172MP	2.3 mils (0.06 mm)	High Density Polyethylene Film (HDPE) 3.0 mils (0.08 mm)		58# Polycoated Kraft Paper (PCK) 4.2 mils (0.11 mm)	
9185MP	5.2 mils (0.13 mm)	High Density Polyethylene Film (HDPE) 3.0 mils (0.08 mm)		58# Polycoated Kraft Paper (PCK) 4.2 mils (0.11 mm)	

Note: The thickness listed is based on a calculation from manufacturing controlled adhesive coat weights using a density of 1.012 g/cc. While past data pages have listed nominal thicknesses, the coat weight (and theoretical caliper) has not changed.

3M™ Adhesive Transfer Tapes with Adhesive 200MP

467MP, 468MP, 467MPF, 468MPF, 7952MP, 7955MP, 7962MP, 7965MP, 9172MP, 9185MP, 9667MP, 9668MP

Typical Physical Properties and Performance Characteristics

I. Adhesion Peel: ASTM D-3330 (Modified)

a. Stainless Steel and 2 mil Aluminum Foil Backing

	15 minute dwell (± 5 minutes)	72 hour dwell RT		72 hour dwell 158F
Product	90°	90°	180°	90°
2.3 mil products (467MP, 467MPF, 7952MP, 7962MP, 9172MP, 9667MP)	47 oz/in 13 N/25 mm	82 oz/in 23 N/25 mm	77 oz/in 21 N/25 mm	168 oz/in 46 N/25 mm
5.2 mil products (468MP, 468MPF, 7955MP, 7965MP, 9185MP, 9668MP)	66 oz/in 18 N/25 mm	118 oz/in 32 N/25 mm	133 oz/in 37 N/25 mm	181 oz/in. 50 N/25mm

b. Adhesion to Other Surfaces: ASTM D3330 modified (90° peel, 2 mil aluminum foil backing with 72 hour dwell)

	2.3 mil products (467MP, 467MPF, 7952MP, 7962MP, 9172MP, 9667MP)		5.2 mil products (468MP, 468MPF, 7955MP, 7965MP, 9185MP, 9668MP)	
Substrate	oz/in	N/25 mm	oz/in	N/25mm
Aluminum	77	21	115	32
ABS	62	17	68	19
Acrylic	61	17	67	19
Glass	80	22	92	25
Polycarbonate	58	16	65	18
Rigid PVC (unplasticized)	62	17	69	19

3M™ Adhesive Transfer Tapes with Adhesive 200MP

467MP, 468MP, 467MPF, 468MPF, 7952MP, 7955MP, 7962MP, 7965MP, 9172MP, 9185MP, 9667MP, 9668MP

Typical Physical
Properties and
Performance
Characteristics
(continued)

II. Static Shear Strength

Temperature	Size	Weight	Minutes
72° (23°C) 50%RH	1" x 1"	1000 grams	10,000+
158°F (70°C) 50% RH	1" x 1"	1000 grams	10,000+
200°F (93°C) 50% RH	1" x 1"	1000	10,000+
350°F (177°C) 50% RH	1" x 1"	500	10,000+
450°F (232°C) 50% RH	1" x 1"	400	60
450°F (232°C) 50% RH	1" x 1"	200	10,000+

*Test terminated at 10,000 minutes

III. Adhesion Retention after Immersion and Exposure (percent retention) Control is 24 hour RT swell on stainless steel, 2 mil foil backing, 90° peel, 12 ipm

	2.3 mil products (467MP, 467MPF, 7952MP, 7962MP, 9172MP, 9667MP)	5.2 mil products (468MP, 468MPF, 7955MP, 7965MP, 9185MP, 9668MP)
Control adhesion value (oz/in)	101	149
Gasoline – 1 hour RT immersion	89%	83%
MEK – 1 hour RT immersion	64%	66%
Weak Acid – 4 hour RT immersion	86%	86%
Weak Base – 4 hour RT immersion	84%	83%
Oil (10W30) – 72 hour, 120°F (49°C) immersion	146%	141%
Water – 100 hours, 70°F (21°C)	105%	116%
Salt Water (5%) – 72 hours, 70°F (21°C)	105%	93%
Warm/Humid – 7 days, 90°F (32°C) and 90% relative humidity	131%	101%
UV Cabinet – 30 days, 70°F (21°C)	147%	93%
Temperature Cycle – 4 hours, 158°F (70°C); 4 hours, -20°F (-29°C); 16 hours, 70°F (21°C)	148%	158%

3M™ Adhesive Transfer Tapes with Adhesive 200MP

467MP, 468MP, 467MPF, 468MPF, 7952MP, 7955MP, 7962MP, 7965MP, 9172MP, 9185MP, 9667MP, 9668MP

Environmental Performance

Humidity Resistance – High humidity has a minimal effect on adhesive performance. Bond strength shows no significant reduction after exposure for 7 days at 90°F (32°C) and 90% relative humidity.

UV Resistance – When properly applied, nameplates and decorative trim parts are not adversely affected by outdoor exposure.

Water Resistance – Immersion in water has no appreciable effect on the bond strength. After 100 hours at room temperature, the high bond strength is maintained.

Temperature Cycling Resistance – High bond strength is maintained after cycling four times through:

4 hours at 158°F (70°C)

4 hours at -20°F (-29°C)

4 hours at 73°F (22°C)

Chemical Resistance – When properly applied, nameplate and decorative trim parts will hold securely after exposure to numerous chemicals including oil, mild acids and alkalis.

Bond Build-up: The bond strength of 3M™ High Performance Acrylic Adhesive 200MP increases as a function of time and temperature

Temperature/Heat Resistance: 3M™ High Performance Acrylic Adhesive 200MP is usable for short periods (minutes, hours) at temperatures up to 400°F (204°C) and for intermittent longer periods (days, weeks) up to 300°F (149°C).

Lower Temperature Service Limit: The glass transition temperature for 3M™ High Performance Acrylic Adhesive 200MP is -31°F (-35°C). Many applications survive below this temperature (factors affecting successful applications include: materials being bonded, dwell at RT before cold exposure, and stress below the TG[i.e.expansion/contraction stresses, impact]). Optimum conditions are: bonding high surface energy materials, longer time at RT before cold exposure, and little or no stress below the TG. The lowest service temperature is -40°F (-40°C).

3M™ Adhesive Transfer Tapes with Adhesive 200MP

467MP, 468MP, 467MPF, 468MPF, 7952MP, 7955MP, 7962MP, 7965MP, 9172MP, 9185MP, 9667MP, 9668MP

Electrical and Thermal Performance

Property	2.3 mil products (467MP, 467MPF, 7952MP, 7962MP, 9172MP, 9667MP)	5.2 mil products (468MP, 468MPF, 7955MP, 7965MP, 9185MP, 9668MP)
Insulation Resistance (test voltage = 100 VDC) Mil-I-46058C	$>1 \times 10^{10}$ ohms	$>1 \times 10^{10}$ ohms
Dielectric Strength – (500 vac, rms[60 hz/sec]) ASTM D149-92	880 volts/mil	600 volts/mil
Breakdown Voltage	1760 volts	3000 volts
Dielectric Constant (at 1kHz) ASTM D150-92	3.40	4.06
Dissipation Factor	0.021	0.022
Tensile Lap Shear – Peak Load ASTM D1002-72 (0.5 sq. in. on #6061 aluminum)	-	55 lbs.
Tensile Lap Shear – Peak Stress ASTM D1002-72	-	109 PSI
Tensile Strength and Elongation ASTM D2360-82	=	51 PSI 1951%
Thermal Conductivity – ASTM C 518, results listed are at 109°F	0.098 BTU-ft/ft ² -hr-F 0.17 watt/m-K	0.101 BTU-ft/ft ² -hr-F 0.18 watt/m-K
Coefficient of Thermal Expansion ASTM D696		
First Heat	28×10^{-5} m/m/C	-6×10^{-5} m/m/C
Second Heat	72×10^{-5} m/m/C	92×10^{-5} m/m/C

Application Ideas

- Long term bonding of graphic nameplates and overlays (“subsurface” printed polycarbonate or polyester) to metal and high surface energy plastics in the aerospace, medical and industrial equipment, automotive, appliance and electronics markets.
- Bonding metal nameplates and rating plates in the aerospace, medical and industrial equipment, automotive, appliance and electronics markets.
- Bonding graphic overlays for membrane switches and for bonding the complete switch to the equipment surface.
- High speed processing of parts in the medical, telecommunications and electronics markets (medical components, durable labels, and flexible circuits).
- Lamination to industrial foams for rotary die-cutting of small gaskets for industrial and electronics markets

3M™ Adhesive Transfer Tapes with Adhesive 200MP

467MP, 468MP, 467MPF, 468MPF, 7952MP, 7955MP, 7962MP, 7965MP, 9172MP, 9185MP, 9667MP, 9668MP

Master Width

Product	Master Width
467MP	48" or 60" (1.22 or 1.52 m)
468MP	
467MPF	54" (1.37 m)
468MPF	
7952MP	48" (1.22 m)
7955MP	
7962MP	
7965MP	
9172MP	
9185MP	
9667MP	54" (1.37 m)
9668MP	

More sizes may be available. Please call 800-223-7427 or talk to your local 3M representative for more information.

Application Techniques

For maximum bond strength (during installation of the final part) the surface should be thoroughly cleaned and dried. Typical cleaning solvents are heptane (for oily surfaces) or isopropyl alcohol for plastics. Use reagent grade solvents since common household materials like rubbing alcohol frequently contain oils to minimize the drying affect on skin and can interfere with the performance of a pressure-sensitive adhesive.

***Note:** Carefully read and follow the manufacturer's precautions and directions for use when working with solvents. These cleaning recommendations may not be in compliance with the rules of certain air quality management districts in California; consult applicable rules before use.

It is necessary to provide pressure during lamination (1.5-20 pli recommended) and during final part installation (10-15 psi) to allow the adhesive to come into direct contact with the substrate. Using a hard edged plastic tool, which is the full width of the laminated part, helps to provide the necessary pressure at the point of lamination. Heat can increase bond strength when bonding to metal parts (generally this same increase is observed at room temperature over longer times, weeks). For plastic parts, the bond strength is not enhanced with the addition of heat.

The ideal adhesive application temperature range is 60°F (15.6°C) to 100°F (38°C). Application is not recommended if the surface temperature is below 50°F (10°C) because the adhesive becomes too firm to adhere readily. Once properly applied, at the recommended application temperature, low temperature holding is generally satisfactory (please refer to section VII of the Typical Physical Properties and Performance Characteristics).

When bonding a thin, smooth, flexible material to a smooth surface, it is generally acceptable to use 2 mils of 3M™ Adhesive 200MP. If a texture is visible on one or both surfaces, the 5 mil 3M adhesive 200MP would be suggested. If both materials are rigid, it may be necessary to use a thicker adhesive to successfully bond the components. 3M™ VHB™ Acrylic Foam

3M™ Adhesive Transfer Tapes with Adhesive 200MP

467MP, 468MP, 467MPF, 468MPF, 7952MP, 7955MP, 7962MP, 7965MP, 9172MP, 9185MP, 9667MP, 9668MP

Application Equipment	Tapes may be required (please refer to the data page 70-0709-3830-6). To apply adhesives in a wide web format, lamination equipment is required to ensure acceptable quality. To learn more about working with pressure-sensitive adhesives please refer to technical bulletin, Lamination Techniques for Converters of Laminating Adhesives (70-0704-1430-8). For additional dispenser information, contact your local 3M sales representative, or the toll free 3M sales assistance number at 1-800-362-3550.
Storage	It is suggested that products are stored at room temperature conditions of 70°F (21°C) and 50% relative humidity.
Shelf Life	If stored properly, product retains its performance and properties for 18 months from date of shipment.
Recognition/Certification	TSCA: This product is defined as an article under the Toxic Substances Control Act and therefore, it is exempt from inventory listing requirements MSDS: 3M has not prepared a MSDS for this product which is not subjected to the MSDS requirements of the Occupational Safety and Health Administration's Hazard Communication Standard, 29 C.F.R.1910.1200(b)(6)(v). When used under reasonable conditions or in accordance with the 3M directions for use, this product should not present a health and safety hazard. However, use or processing of the product in a manner not in accordance with the directions for use may affect its performance and present potential health and safety hazards. UL: These products have been recognized by Underwriters Laboratories, Inc. under Standard UL 969, Marking and Labeling Systems Materials Component. For more information on the UL Certification, please visit the website at http://www.3M.com/converter, select UL Recognized Materials, then select the specific product area. Military: Meets MIL-P-19834 Note: One of 3M's core values is to respect our social and physical environment. 3M is committed to comply with ever-changing, global, regulatory and consumer environmental, health, and safety (EHS) requirements. As a service to our customers, 3M is providing information on the regulatory status of many 3M products. Further regulation information including that for OSHA, USCPSI, FDA, California Proposition 65, READY and RoHS, can be found at 3M.com/regs.
Technical Information	The technical information and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed. It has been prepared from testing that was performed using standard test methods, and tested equipment that is calibrated in compliance to ISO9001 and operated by trained professionals in controlled environments. The data should be considered representative or typical only and should not be used for specification purposes. 3M reserves the right to make changes to the design, construction and technical data of products without prior warning.

3M™ Adhesive Transfer Tapes with Adhesive 200MP

467MP, 468MP, 467MPF, 468MPF, 7952MP, 7955MP, 7962MP, 7965MP, 9172MP, 9185MP, 9667MP, 9668MP

Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluation the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy and Disclaimer

Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price

Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence, or strict liability.

ISO 9001

This Industrial Adhesives & Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.



For more information contact your local 3M representative or call 800-223-7427



Industrial Adhesives & Tapes Division
Converter Markets
3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-223-7427 651-778-4244 (fax)
www.3M.com/converter

3M is a trademark of 3M Company
© 3M 2014
70-0709-3858-7 (3/14)