


RCA Plugs

174-0051-E, 174-0052-E, 174-0053-E, 174-0054-E

KOBICONN

RCA Plugs



Dimensions: mm (In.)

SPECIFICATIONS

Rating:	34VAC/DC 2A
Dielectric strength:	250VAC for one minute
Insulation resistance:	100 MΩ min. @ 500VDC
Contact resistance:	30 mΩ max.
Insertion force:	3 Kgf. max.
Extraction force:	0.1 -3 Kgf
Handle:	ABS resin
Insulator:	ABS
Center pin:	nickel plated brass
RoHS Compliant	

Pin	Color
174-0051-E	Red
174-0052-E	Black
174-0053-E	White
174-0054-E	Yellow

Date Last Revised: 12-9-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 300918

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[174-0052-E](#) [174-0053-E](#) [174-0051-E](#) [174-0054-E](#)