


**PRODUCT  
DATA SHEET**

Type	Size	Rating	Description	Part No.
Incandescent	T5	24V 0.04A	T-1½ Bead Seal Lamp	687BS



Drawing Not To Scale  
All Dimensions In mm

**PHOTOMETRY DATA**

TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE (Hours)
	Min.	Nom.	Max.	Min.	Nom.	Max.	
24	36	40	44	2.25	3.0	3.75	10,000

**NOTES:**

- 1) C-2F Filament Shape.
- 2) Lead wires 0.25mm diameter x 25.4mm MIN. long, with tinned finish.
- 3) Other Leadwire lengths to be supplied according to purchase order.

Issue No.	Date	C.N. No.	Drawn	Tech	QA	M & P	Sales
1	4/2/97		NR				