

Cable gland - HC-K-KV-M16(5-10) - 1690613

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Plastic screw connection up to 5 bar, thread length: 8 mm, cable diameter: 5 - 10 mm, WAF 20, screw connection: M16

The illustration shows version
HC-K-KV-M20

Key commercial data

package_quantity	25
GTIN	4017918822668

Technical data

Dimensions

Wrench size, union nut	20 mm
Wrench size, support	20 mm
Length of the connecting thread	8 mm
External cable diameter	5 mm ... 10 mm
Conductor sealing range	5.00 mm ... 10.00 mm

Ambient conditions

Degree of protection	IP68, to 5 bar
Degree of protection	IP68 (Up to 5 bar)
Ambient temperature (operation)	-20 °C ... 100 °C

General

Type of the screw connection	M16
Cable gland material	Polyamide
Seal material	Neoprene
Cable seal material	Neoprene
Thread type on connection side	M16
Tightening torque, union nut	2.00 Nm
Inflammability class according to UL 94	V2
Color	Silver gray

classifications

eCl@ss

eCl@ss 4.0	27141209
------------	----------

Cable gland - HC-K-KV-M16(5-10) - 1690613

classifications

eCl@ss

eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

approvals

GOST /


Approval details

 GOST
--

Drawings

Cable gland - HC-K-KV-M16(5-10) - 1690613

Dimensioned drawing



Dimensional drawing

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>