



REVISIONS				DATE	APPROVED
P	F	LTR	DESCRIPTION		
1		B	REVISED PER FC 0220-0213-94	11/22/94	11/22/94




1. FOR USE WITH RG-402/U
.141 SEMI-RIGID CABLE

2. .250 MAX PANEL THK

3. USE INSTRUCTION SHEET 670



SUGGESTED PANEL CUTOUT



RECOMMENDED STRIP LENGTH

5	1	JACK ASSY	228503-1
4	1	ADAPTOR ASSY	228946-1
3	1	JAM NUT	1-329631-2
2	1	LOCK WASHER	1-329632-2
1	1	GASKET	329633
ITEM	QTY	DESCRIPTION	PART NO

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION

BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PENDING PATENTS.

© COPYRIGHT 19

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. TOLERANCES ON DECIMALS: .005

MATERIAL

FINISH

CONTRACT NO

DR T. D. Smith 9/20/82

CHK R. L. Vanturel 8-26-82

APPD R. H. [Signature] 8/14/82

APPD T. D. Smith 8/15/82

DSGN APPD

OTHER APPD

AMP

AMP INCORPORATED
Harrisburg, Pa. 17105

NAME

CONNECTOR, COAXIAL, RF
JACK, REAR MOUNTED, SERIES TNC

SIZE

A

FSCM NO

00779

DRAWING NO

228502-1

SCALE NTS

SHEET