





(1,27mm) .050"


FLE SERIES



FLE-110-01-G-DV



FLE-140-01-G-DV



FLE-120-01-G-DV

COST EFFECTIVE RELIABLE SOCKET

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?FLE

Insulator Material:

Black Liquid
Crystal Polymer

Contact Material:

Phosphor Bronze

Plating:

Au over 50µ" (1,27µm) Ni

Current Rating:

1.75A @ 80°C ambient

Operating Temp Range:

-55°C to +125°C

Contact Resistance:

15mΩ max

Insertion Depth:

(1,83mm) .072" to

(4,37mm) .172" or

pass-through

Insertion Force:

(Single contact only)

1.5oz (0,42N)

Normal Force:

100 grams (0,98N)

Withdrawal Force:

(Single contact only)

1.5oz (0,42N)

Max Cycles:

100+

RoHS Compliant:

Yes

Processing:

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0,10mm) .004" max



Tiger Beam™
contact

Ideal for
pass-through
applications

Surface
Mount

(1,27mm) .050"
micro pitch

Available with optional
Pick & Place pads

FLE

-

1

NO. PINS
PER ROW

-

01

PLATING
OPTION

-

DV

OPTIONS

02 thru 50

-G
= 10µ" (0,25µm) Gold

Note: Other gold plating options
available. Contact Samtec.

-A

= Alignment Pin
(Metal or plastic at
Samtec discretion)
(3 positions minimum)

-K

= (4,25mm) .167" DIA
Polyimide film
Pick & Place Pad
(5 positions minimum)

-P

= Metal Pick &
Place Pad
(5 positions minimum)


-TR

= Tape & Reel

TAPE & REEL AVAILABILITY

No tooling charges.
Minimum order is the lesser of
a full reel quantity or 125 pieces.
Order any quantity above minimum.
In-house design, manufacture.
Quick turn-around.

Call Samtec for specifications
and ordering information.



Note: Some lengths, styles
and options are non-standard,
non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC SILICON VALLEY • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-8329
SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 SAMTEC UNITED KINGDOM • Tel: 44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292 SAMTEC ISRAEL • Tel: 972-3-7526600
SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-61103766 SAMTEC TAIWAN • Tel: 886-2-2735-6109
SAMTEC HONG KONG • Tel: 852-26904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC ANZ • Tel: 613 9512 7747 SAMTEC SOUTH AFRICA • Tel: 27 11 452 8112