

# Stylus® Alkaline Battery-Powered Pen Light

| FL 1 STANDARD                                                                     | WHITE LED           |
|-----------------------------------------------------------------------------------|---------------------|
|  | <b>11</b><br>LUMENS |
|  | <b>24h</b>          |
|  | <b>24m</b>          |
|  | <b>140cd</b>        |

| FL 1 STANDARD                                                                     | BLUE LED           |
|-----------------------------------------------------------------------------------|--------------------|
|  | <b>2</b><br>LUMENS |
|  | <b>24h</b>         |
|  | <b>21m</b>         |
|  | <b>110cd</b>       |



| FL 1 STANDARD                                                                       | GREEN LED          |
|-------------------------------------------------------------------------------------|--------------------|
|  | <b>7</b><br>LUMENS |
|  | <b>24h</b>         |
|  | <b>15m</b>         |
|  | <b>59cd</b>        |

| FL 1 STANDARD                                                                       | RED LED            |
|-------------------------------------------------------------------------------------|--------------------|
|  | <b>2</b><br>LUMENS |
|  | <b>24h</b>         |
|  | <b>15m</b>         |
|  | <b>53cd</b>        |

Case Material: machined aluminum case with anodized finish and non-slip, knurled grip. Available in black, gold or silver, red, blue, US Flag

Dimensions/Weight: Length: 6.21"; 15.17 cm Diameter: 0.375"; 0.95 cm 1.1 oz; 31.19 grams\*

Light Source: High intensity 5mm LED, impervious to shock with a 100,000 hour lifetime  
Available in White, Blue (470nm), Red (624nm), Green (527nm), UV (365nm) or IR (880nm)

On/Off: Features a momentary blink switch and constant "on"

Battery: 3 "AAAA" size alkaline batteries.

Features: High intensity LED  
Individually serialized for positive identification  
IPX4/water-resistant. 2 meter impact resistance tested  
Removable pocket clip.  
Glare guard protector included in package  
UL model available

Approvals\*\*: UL Classified: Intrinsic Safety for Hazardous Locations; Class I, Div.1, Groups A,B,C,D, T3C "Classified" (applies to specific model)



C-UL UL Classified: Intrinsic Safety for Hazardous Locations; Class I, Div.1, Groups A,B,C,D, T3C; "Exia" (applies to specific model)

ATEX: II 1G EEx ia IIC T1; DEMKO 04 ATEX 0410949 (applies only to Black case/White or Blue LED combinations)

Most models meet applicable European Community Directives.

Warranty: Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction

\*With battery (included in purchase).

\*\*See product for specific ratings.

| Item                                    | UPC            | Part # |
|-----------------------------------------|----------------|--------|
| Stylus Black with Red LED               | 080926-65006-0 | 65006  |
| Stylus Black with Blue LED              | 080926-65022-0 | 65022  |
| Stylus Black with Green LED             | 080926-65020-6 | 65020  |
| Stylus Black with White LED             | 080926-65018-3 | 65018  |
| Stylus UL Listed Black with White LED   | 080926-65058-9 | 65058  |
| Stylus Black with UV LED                | 080926-65069-5 | 65069  |
| Stylus OD with IR LED                   | 080926-65186-9 | 65186  |
| Stylus US Flag with White LED           | 080926-65080-0 | 65080  |
| See reverse for additional part numbers |                |        |





| Item                                              | UPC            | Part # |
|---------------------------------------------------|----------------|--------|
| Lanyard with Push Button Slide <i>(not shown)</i> | 080926-72024-4 | 72024  |
| AAAA Batteries – 6 pack                           | 080926-65030-5 | 65030  |