


| 6           |           | 5              |         | 4       |         | 3       |         | 2               |         | 1                     |                   |
|-------------|-----------|----------------|---------|---------|---------|---------|---------|-----------------|---------|-----------------------|-------------------|
| PART NUMBER | WIRE SIZE | "W"            | "C" MIN | "E" MAX | "B" MIN | "L" MAX | "A" MIN | STOCK THICKNESS | "F" MAX | AVAILABLE STUD SIZE   | DRWG. NO. SD02051 |
| L-395-      | 4/0       | 1.102<br>1.128 | .822    | 1.653   | .734    | 2.242   | .622    | .099<br>.102    | .865    | 14, 38, 76,<br>12, 58 | A                 |
| L-398-      | 4/0       | 1.227<br>1.253 | 1.292   | 2.123   | .734    | 2.765   | .622    | .099<br>.102    | .865    | 58, 34, 78            |                   |

# VERSAKRIMP



MATERIAL: COPPER  
PLATING: ELECTRO-TIN

| STUD SIZE |       | ±.005 "D" |
|-----------|-------|-----------|
| 14        | 1/4"  | .265      |
| 56        | 5/16" | .328      |
| 38        | 3/8"  | .390      |
| 76        | 7/16" | .453      |
| 12        | 1/2"  | .515      |
| 58        | 5/8"  | .656      |
| 34        | 3/4"  | .781      |
| 78        | 7/8"  | .906      |

# CUSTOMER DRAWING

| DIMENSIONS SHOWN (METRIC) INCH                           |             |        |
|----------------------------------------------------------|-------------|--------|
| UNLESS OTHERWISE SPECIFIED<br>TOLERANCES: ANGULAR ± 1/2° |             |        |
|                                                          | INCH        | METRIC |
| 3 PLACE                                                  | ± .005      | ± 0.13 |
| 2 PLACE                                                  | ± .01       | ± 0.25 |
| 1 PLACE                                                  | ± ---       | ± ---  |
| DRAFT WHERE APPLICABLE MUST<br>REMAIN WITHIN DIMENSIONS  |             |        |
| DRWG. BY LEM                                             | CHK'D. BY   |        |
| APP'D. BY                                                | SCALE NO:NE |        |

| REVISE ONLY ON CAD SYSTEM                          |                                                                                                                            |                   |                 |
|----------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------|-------------------|-----------------|
| TITLE "L" RING TONGUE TERMINAL                     |                                                                                                                            |                   |                 |
| moLEX ETC INC.<br>PINELLAS PARK, FLA. 33781 U.S.A. |                                                                                                                            | SHEET NO.         | DATE 70 /03 /02 |
| PART NO. SEE CHART                                 |                                                                                                                            | DRWG. NO. SD02051 |                 |
| FILE NAME<br>SDL395 DGN                            | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX-ETC INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION. |                   | DIV. SIZE A     |

|      |                                                    |
|------|----------------------------------------------------|
|      |                                                    |
| A    | ADD STUD SIZE &<br>UPDATE TO CAD<br>ET970953 08/20 |
| LTR. | REVISIONS                                          |