


Distributed by:

**JAMECO**<sup>®</sup>  
ELECTRONICS

**www.Jameco.com ♦ 1-800-831-4242**

The content and copyrights of the attached  
material are the property of its owner.

Jameco Part Number 241294



| P/N    | MFG         | Resistance (Ohms) | Characteristics             |                      |                      |             |
|--------|-------------|-------------------|-----------------------------|----------------------|----------------------|-------------|
| 241235 | 3006P-1-101 | 100               | Total Mechanical Travel     | 22±2 cycles          | Starting Torque      | 30mN.m      |
| 241294 | 3006P-1-103 | 10,000            |                             |                      |                      |             |
| 241332 | 3006P-1-104 | 100,000           | Withstand Voltage           | 101.3KPa 600V        | Terminal Resistance  | ≤2G Ω       |
| 241374 | 3006P-1-105 | 1,000,000         |                             | 8.5KPa 350V          |                      |             |
| 241307 | 3006P-1-203 | 20,000            | Effective Electrical Travel | 22±2 cycles          | Standard Packaging   | 25pcs/tube  |
| 241350 | 3006P-1-204 | 200,000           |                             |                      |                      |             |
| 241252 | 3006P-1-501 | 500               | Rated Power                 | +70℃ 0.75W           | Mechanical Endurance | 200 cycles  |
| 241286 | 3006P-1-502 | 5,000             |                             | +125℃ 0W             |                      | △R≤±3%      |
| 241323 | 3006P-1-503 | 50,000            | Insulation Resistance       | R <sub>i</sub> ≥1G Ω | Temperature Range    | -55℃ ~+125℃ |