





8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
G	ECN 5837: ADDED LOGO	11/15/11	D. CASTRO
-	-	-	-
-	-	-	-
-	-	-	-

P/N	LENGTH	
	FEET	METERS
CTLDVI-DL-MM-3	3.0	.92
CTLDVI-DL-MM-5	5.0	1.52
CTLDVI-DL-MM-10	10.0	3.05
CTLDVI-DL-MM-15	15.0	4.57



NOTES:

1. CABLES TO BE TESTED FOR CONTINUITY
2. CABLES TO BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPEC. PS-0031
3. DUST COVERS INSTALLED FOR SHIPPING (NOT SHOWN).

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ±.005 PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	DRAWN BY Bill_Zhang	10/15-'08			
	CHECKED BY Frank_Mao	10/15-'08	CATEGORY VIDEO		
	APPROVED BY Thomas_Lu	10/15-'08	PRODUCT DESCRIPTION DVI-DL M/DVI-DL M W/FERRITE		
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	SIZE A	FSCM NO. 43321	DWG. NO. CTLDVI-DL-MM	REV. G
	COLOR VARIATIONS MAY OCCUR	SCALE: NONE	CAD FILE: CTLDVI-DL-MM.SLDDRW		SHEET 1 OF 1