




13 12 11 10 9 8 7 6 5 4 3 2 1



ITEM	DESCRIPTION
1	SCREW
2	EXTERNAL THREAD COVER
3	INSERT
4	GASKET
5	GROMMET
6	EXTERNAL THREAD NUT

C29200NOT****

SERIES _____
C29= EXTERNAL THREAD FORM C MICRO
POLES _____
2= 2 POLE & 3= 3 POLE
THREAD _____
00 = EXTERNAL THREAD
MATERIAL AND HOUSING COLOR _____
G= PA6 GREY, N= PA6 BLACK, W= PA6 BLACK V0, T= TRANSPARENT
GROUND POSITION _____
0= UNMOUNTED, 2= H12, 3=H3, 6 =H6 & 9= H9
SCREW AND GASKET _____
U= PROFILE SILICON GASKET AND IP67 SCREW
T= PROFILE NBR GASKET AND IP67 SCREW
NON STANDARD PACKAGING _____
CN= BULK PACK UN-MOUNTED
SN= BULK PACK MOUNTED
ADDITIONAL CODES _____
SA= UL AGENCY APPROVAL

NOTES:

1. FOR SPECIFIC PART NUMBERS PLEASE CONTACT SALES OR CONSULT THE INTELLIGENT PART NUMBERS IN THE TABLE ATTACHED
2. PACKAGING SPECIFICATION: PLEASE SEE PK-121201-001
3. PRODUCT SPECIFICATION: PLEASE SEE PS-121201-001
4. CABLE SIZES 3 - 5.5 MM DIAMETER
5. TIGHTENING TORQUES: SEE PS-121201-001
6. GROUND POSITION SHOWN H12

LAST INSPECTION NUMBER 9

ADDED PART NUMBER EC NO: IPG2013-1466 DRW:DSHEA 2013/03/21 CHKD:SMGREVY 2013/03/21 APPR:STGERFFIN 2013/04/08	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
							TITLE EXTERNAL THREAD C29 SERIES 121205		molex	SHEET NO. 1 OF 2	
			4 PLACES	± ---	± ---	DRAWN BY DMAHER_WEU	DATE 2010/05/10	DOCUMENT NO. SD-121205-001			
			3 PLACES	± ---	± ---	CHECKED BY	DATE				
			2 PLACES	± 0.1	± ---	APPROVED BY	DATE				
			1 PLACE	± 0.2	± ---	EFOLAN	2010/05/25				
			0 PLACE	± ---	± ---	MATERIAL NO.					
			ANGULAR ± ---°		SEE SHEET 2						
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

PART NUMBER	mPm NUMBER	DESCRIPTION
1212050001	C29200N0T	FORM C MICRO 2 POLE BLACK NBR GASKET
1212050002	C29200G0T	FORM C MICRO 2 POLE GREY NBR GASKET
1212050003	C29200W0TSA	FORM C MICRO 2 POLE BLACK UL V0 NBR GASKET
1212050004	C29200T0T	FORM C MICRO 2 POLE TRANSPARENT NBR GASKET
1212050005	C29300N0T	FORM C MICRO 3 POLE BLACK NBR GASKET
1212050006	C29300G0T	FORM C MICRO 3 POLE GREY NBR GASKET
1212050007	C29300W0TSA	FORM C MICRO 3 POLE BLACK UL V0 NBR GASKET
1212050008	C29300T0T	FORM C MICRO 3 POLE TRANSPARENT NBR GASKET
1212050009	C29200N0TCN	FORM C MICRO 2 POLE BLACK NBR GASKET
1212050011	C29200W0TCNSA	FORM C MICRO 2 POLE BLACK UL V0 NBR GASKET
1212050012	C29200N2TSN	FORM C MICRO 2 POLE BLACK NBR GASKET
1212050013	C29200W0USA	FORM C MICRO 2 POLE BLACK UL V0 SILICONE GASKET
1212050014	C29300W0USA	FORM C MICRO 3 POLE BLACK UL V0 SILICONE GASKET
1212050015	C29300W0TCNSA	FORM C MICRO 3 POLE BLK UL V0 PA6 NBR BULK
1212050016	C29200W0UCNSA	FORM C MICRO 2 POLE BLK UL V0 PA6 SILICONE BULK
1212050017	C29300W0UCNSA	FORM C MICRO 3 POLE BLK UL V0 PA6 SILICONE BULK
1212050018	C29300G2TSN	FORM C MICRO 3 POLE GREY NBR GASKET
1212050019	C29200T2TSN	FORM C MICRO 2 POLE TRANSPARENT NBR GASKET
1212050020	C29200W6TSNSA	FORM C MICRO 2 POLE BLK UL V0 PA6 NBR BULK
1212050021	C29300N2TSN	FORM C MICRO 3 POLE BLACK NBR GASKET
1212050022	C29300N0U	FORM C MICRO 3 POLE BLACK SILICONE GASKET
1212050023	C29200W2TSNSA	FORM C MICRO 2 POLE BLK UL V0 PA6 NBR BULK
1212050024	C29300N0TCN	FORM C MICRO 3 POLE BLACK NBR GASKET

SEE SHEET 1 EC NO: IPG2013-1466 DRAWN BY: DRWN:JSHEA 2013/03/21 CHKD:SMCGREYV 2013/03/21 APPR:STGRJFFIN 2013/04/08	QUALITY SYMBOLS  =0  =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 1:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
				DRAWN BY DMAHER_WEU	DATE 2010/05/10	TITLE EXTERNAL THREAD C29 SERIES 121205				
				CHECKED BY		DATE				
				APPROVED BY EFOLAN		DATE 2010/05/25				
				MATERIAL NO.		DOCUMENT NO. SD-121205-001		SHEET NO. 2 OF 2		
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						