

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130106-0097](#)
Status: **Active**
Overview: [Stringlights](#)
Description: Super-Safeway™ Assembled Rubber Stringlight 200W 14/3 SOOW 1.52m (5.0') Lead Locking with Guard 3.04m (10.0') Overall Length 30.48m (100.0')

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
Series [130106](#)
NEMA Configuration NEMA L5-15
NEMA Rating Rain Tight
Outlet None
Overview [Stringlights](#)
Product Literature Order No 987650-8055
Product Name Super-Safeway™
Type String Lights
UPC 78678804132
Woodhead Yes

Physical

Cord Length - Primary 3.04m (10.0')
Cord Length - Secondary N/A
Depth 46.48mm (1.830")
Duty Industrial
Guard Included 362
Guard Type N/A
Height 101.60mm (4.000")
Length 30.48m (100.0')
Material - Guard #8 Gauge Zinc-plated Steel
Mounting Style Stringer
Net Weight 163.290/kg
Packaging Type Carton
Socket Construction Assembled

Electrical

Bulb Type Incandescent
Cord Type - Primary 14/3 SOOW
Lamp Type A21
Lamp Wattage - Maximum 200W
Lumens 2000
On/Off Switch No
Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Old Part Number 310243



image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[130106Series](#)