





PART NAME	NBF SERIES PLASTIC NEMA BOX		PART No.	NBF-32012 & NBF-32112 & NBF-32212 & NBF-32312 & NBF-32412		REVISION DATE	8/12/2010
MATERIAL	FLAMMABILITY RATING	CONTINUOUS OPERATING TEMP.	FINISH: BODY_____ LIGHT GRAY COVER_____ LIGHT GRAY OR CLEAR LATCHES & HINGES_____ PLASTIC WALL MOUNTING BRACKETS__ STAINLESS STEEL & HARDWARE				
ABS	UL94-HB	-40°C ~ +60°C / -40°F ~ 140°F					
CLEAR PC	UL94-V0 UV STABILIZED	-40°C ~ +130°C / -40°F ~ 266°F					
ABS / PC BLEND	UL94-5VA	-40°C ~ +85°C / -40°F ~ 185°F					
PBT / PC BLEND	UL94-5VA + UV (f1)	-40°C ~ +75°C / -40°F ~ 167°F					




BODY




Ø.134in [3.40mm]
FOR M4 x 10mm LG. SELF-TAPPING SCREWS (ABS VERSIONS ONLY)
M4 THREADED INSERTS ON ALL OTHER VERSIONS USE M4 x 8mm LG. MACHINE SCREWS. 4 PLCS.




Ø.134in [3.40mm]
FOR M4 x 10mm LG. SELF-TAPPING SCREWS 4 PLCS.



ASSEMBLY



COVER



NOTES:

- 1) UNIT COMES COMPLETE WITH (4) WALL MOUNTING BRACKETS & (4) M4 x 10mm LG. SELF-TAPPING SCREWS. (NOT SHOWN)
- 2) BOXES DESIGNED TO MEET FOLLOWING STANDARDS: NEMA 1,2,4,4X, AND IEC529-IP65 REQUIREMENTS.

TOLERANCE:

ALL DIMENSIONS HAVE ±0.039in [±1mm] TOLERANCE UNLESS OTHERWISE SPECIFIED.

PART NO.	MATERIAL		USE
	BODY	COVER	
NBF-32012	ABS	ABS	INDOOR
NBF-32112	ABS / PC	ABS / PC	INDOOR
NBF-32212	ABS / PC	CLEAR PC	INDOOR
NBF-32312	PBT / PC	PBT / PC	OUTDOOR
NBF-32412	PBT / PC	CLEAR PC	OUTDOOR