

PANASONIC 12 VOLT LEAD-ACID BATTERIES



Part Number	Volts	Capacity 20Hr. Rate	Dimensions (Inches)			Weight (Lbs)	Cross Reference	Termination
			Length	Width	Height Inc. Term			
LEAD-12V-1.3P	12	1.3	3.82	1.87	2.16	1.30	LC-R121R3P, LCR12V1.3P	.187 TAB
LEAD-12V-2P	12	2.0	6.97	.94	2.52	1.40	LC-T122PU	.187 TAB
LEAD-TA122PU	12	2.0	7.17	.94	2.42	1.40	LC-TA122PU	PRESSURE
LEAD-12V-2.2P	12	2.2	6.97	1.34	2.60	1.76	LC-R122R2P, LCR12V2.2P	.187 TAB
LEAD-12V-3.4P	12	3.4	5.28	2.64	2.60	2.65	LC-R123R4P, LCR12V3.4P	.187 TAB
LEAD-12V-4P			NLA — USE LEAD 12V-5P				LC-RB124P	
LEAD-12V-5P	12	5.0	3.54	2.76	4.26	4.25	LC-R125P, LCR12V5P	.187 TAB
LEAD-12V-6.5P			NLA — USE LEAD 12V-7.2P				LCR-12V-6.5P	
LEAD-12V-6.5P-250			NLA — USE LEAD 12V-7.2P-250				LCR-12V-6.5P1	
LEAD-12V-7.2P	12	7.2	5.95	2.54	3.94	5.45	LC-R127R2P, LCR12V7.2P	.187 TAB
LEAD-12V-7.2-250	12	7.2	5.95	2.54	3.94	5.45	LC-R127R2P1	.250 TAB
LEAD-12V-12P	12	12.0	5.95	3.86	3.90	8.30	LC-R1212P, LCR12V12PF, LC-RA1212P	.250 TAB
LEAD-12V-17P	12	17.0	7.13	2.99	6.57	14.3	LC-RC1217P, LCR12V17CP, LC-RD121D	NUT & BOLT
LEAD-12V-20P	12	20.0	7.13	2.99	6.57	14.5	LC-X1220P	NUT & BOLT
LEAD-12V-24PB	NLA — USE LEAD 12V-28PB (NOTE REVERSED POSITIVE AND NEGATIVE)						LCR-12V-24P	
LEAD-12V-28PB	12	28.0	6.50	4.90	7.10	24.30	LC-X1228P	NUT & BOLT
LEAD-12V-28PTP	12	28.0	6.50	4.90	6.90	24.30	LC-X1228AP	THREADED POST
LEAD-12V-33P	12	33.0	7.70	5.12	7.09	26.5	LC-LA1233P, LCL12V33AP	NUT & BOLT
LEAD-12V-38P			NLA — USE LEAD 12V-42P				LCR-12V-38P	
LEAD-12V-42P	12	42.0	7.75	6.49	7.08	35.20	LC-X1242P	NUT & BOLT
LEAD-12V-42PTP	12	42.0	7.75	6.49	7.08	35.20	LC-X1242AP	THREADED POST
LEAD-12V-65P	12	65.0	13.78	6.54	6.89	44.1	LC-L1265P, LCL12V65P, LC-X1265P	NUT & BOLT
LEAD-12V-100P	12	100.0	16.03	6.82	9.29	72.8	LCR12V100AP, LC-XA12100P	NUT & BOLT

Part Number	Volts	Capacity 20Hr. Rate	Dimensions (Inches)			Weight (Lbs)	Cross Reference	Termination
			Length	Width	Height Inc. Term			
HIGH POWER SERIES								
LEAD-UPRW1220P	12	20.0	5.51	1.51	3.99	2.98	UP-RW 1220P	.187 TAB
LEAD-UPRW1220P-250	12	20.0	5.51	1.51	3.99	2.98	UP-RW1220P1	.250 TAB
LEAD-UPRW1245P	12	45.0	5.95	2.54	3.99	5.73	UP-RW1245P	.187 TAB
LEAD-UPRW1245P-250	12	45.0	5.95	2.54	3.99	5.73	UP-RW1245P1	.250 TAB

NOTES