

Part Number: SMT-1027-S-R



Features

Mounting: Surface Mount
Frequency: 2700 +/- 500Hz
This part is RoHS 2002/95/EC Compliant.


Electrical Specifications

Operating Voltage	1-2 Vp-p
Rated Current (Max.)	80 mA
Rated Voltage	1.5 Vp-p
Resonant Frequency	27 +/- 500Hz
Sound Pressure Level @ 10 cm (Min.)	85 dBA

Case: LCP
Weight: 0.8g
Pin Material: Tin Plated Phosphor Bronze
Environmentally friendly.

Mechanical

Dimensions are in millimeters, tolerance is ± 0.5 unless otherwise specified.



Performance

Typical SPL vs. Frequency



For application notes and detail drawing specifications, please consult www.projectsunlimited.com.

Specifications subject to change without notice.

© 2005, Projects Unlimited Inc., All Rights Reserved.