

Super Vu-Tron® Multi-Conductor Type S00W

90°C 600 Volt UL/CSA Portable Cord

Product Construction:

Conductors:

- 14 through 10 AWG fully annealed stranded bare copper per ASTM B-174

Insulation:

- Premium-grade, color-coded 90°C EPDM
- Color code: See chart below

Jacket:

- Super Vu-Tron® 90°C, black
- Temperature range: -40°C to +90°C

Jacket Marking:

- CAROL SUPER VU-TRON (SIZE) (mm²)
90°C (UL) WATER RESISTANT S00W CSA
(-40°C) FT-2 P-7K-123033 MSHA 600 VOLT
RoHS MADE IN USA

Applications:

- Control circuits
- Tools
- Heavy industrial, processing and construction equipment

Features:

- Extra-flexible stranding
- Abrasion-resistant
- Resists oils and solvents
- Flame-resistant
- Ozone-resistant
- 90°C rated conductors and jacket
- Water-resistant
- UL Listed and CSA Certified for indoor and outdoor use
- Ozone-sunlight (UV)- and weather-resistant

Industry Approvals:

- UL Flexible Cord - UL Subject 62
- CSA Flexible Cord - C22.2-49
- MSHA Approved
- RoHS Compliant

Packaging:

- 5- through 8-conductor available on 250' (76.2 m), 500' (152.4 m), and 1000' (304.8 m) reels
- 9+ cond. available on long-length reels
- Other put-ups available on special order

COLOR CODE CHART

NO. OF COND.	COLOR	TRACER	NO. OF COND.	COLOR	TRACER
1	Black	—	12	Black	White
2	White	—	13	Red	White
3	Red	—	14	Green	White
4	Green	—	15	Blue	White
5	Orange	—	16	Black	Red
6	Blue	—	17	White	Red
7	White	Black	18	Orange	Red
8	Red	Black	19	Blue	Red
9	Green	Black	20	Red	Green
10	Orange	Black	21	Orange	Green
11	Blue	Black	Note: Colors repeat after 21 conductors. Refer to page 18 for color diagram.		



TYPE S00W - 600 VOLT - UL/CSA

CATALOG NUMBER	NO. OF COND.	AWG SIZE	COND. STRAND	NOMINAL INS. THICKNESS		NOMINAL O.D.		CURRENT AMPS†	APPROX. NET WT. LBS/M ^(S)
				INCHES	mm	INCHES	mm		
09405	5	14	41/30	0.045	1.14	0.645	16.38	12.0	269
09406	6	14	41/30	0.045	1.14	0.710	18.03	12.0	317
09407	7	14	41/30	0.045	1.14	0.710	18.03	12.0	347
09408	8	14	41/30	0.045	1.14	0.760	19.30	10.5	430
09409*	9	14	41/30	0.045	1.14	0.830	21.08	10.5	417
09410	10	14	41/30	0.045	1.14	0.820	20.83	10.5	427
09412	12	14	41/30	0.045	1.14	0.855	21.72	7.5	493
09414	14	14	41/30	0.045	1.14	1.000	25.40	7.5	601
09416	16	14	41/30	0.045	1.14	1.030	26.16	7.5	678
09418*	18	14	41/30	0.045	1.14	1.100	27.94	7.5	720
09420	20	14	41/30	0.045	1.14	1.120	28.45	7.5	806
09424	24	14	41/30	0.045	1.14	1.260	32.00	6.7	1003
09428*	28	14	41/30	0.045	1.14	1.330	33.78	6.7	1080
09430*	30	14	41/30	0.045	1.14	1.335	33.91	6.0	1153
09205	5	12	65/30	0.045	1.14	0.715	18.16	16.0	333
09206	6	12	65/30	0.045	1.14	0.740	18.80	16.0	412
09207	7	12	65/30	0.045	1.14	0.790	20.07	16.0	465
09208	8	12	65/30	0.045	1.14	0.825	20.96	14.0	526
09209	9	12	65/30	0.045	1.14	0.900	22.86	14.0	517
09210	10	12	65/30	0.045	1.14	1.000	25.40	14.0	649
09212	12	12	65/30	0.045	1.14	1.010	25.65	10.0	669
09214	14	12	65/30	0.045	1.14	1.020	25.91	10.0	731
09216	16	12	65/30	0.045	1.14	1.135	28.83	10.0	933
09218*	18	12	65/30	0.045	1.14	1.175	29.85	10.0	920
09220	20	12	65/30	0.045	1.14	1.170	29.72	10.0	989
09224	24	12	65/30	0.045	1.14	1.435	36.45	9.0	1273
09226	26	12	65/30	0.045	1.14	1.380	35.05	9.0	1324
09227*	27	12	65/30	0.045	1.14	1.455	37.72	9.0	1325
09228*	28	12	65/30	0.045	1.14	1.500	38.10	9.0	1355
09230	30	12	65/30	0.045	1.14	1.455	36.96	9.0	1492
09005	5	10	104/30	0.045	1.14	0.770	19.56	20.0	472
09006	6	10	104/30	0.045	1.14	0.875	22.23	20.0	565
09007	7	10	104/30	0.045	1.14	0.900	22.86	20.0	552
09008*	8	10	104/30	0.045	1.14	0.935	23.75	17.5	682
09010	10	10	104/30	0.045	1.14	1.020	25.91	17.5	758
09012	12	10	104/30	0.045	1.14	1.070	27.18	12.5	871
09016*	16	10	104/30	0.045	1.14	1.230	31.24	12.5	1147
09020*	20	10	104/30	0.045	1.14	1.325	33.66	12.5	1445

† Values shown are for current-carrying conductors. A grounding conductor, or one which carries only the unbalance current from other conductors, is NOT counted in determining current carrying capacity. Ampacities based on NEC table 400.5(A).

* Non-stock item; minimum quantity purchase required.

^(S) Actual shipping weight may vary.