




8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—

1

HOUSING MATERIAL: THERMOPLASTIC, COLOR—NATURAL.

2

CONTACT MATERIAL: COPPER ALLOY.

3

FINISH:
MATING AREA: MEETS THE PERFORMANCE REQUIREMENTS OF PRODUCT SPECIFICATION 108—9063; BASED ON TELCORDIA DR—1217—CORE APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
SOLDER TAILS AREA: TIN—LEAD PLATED.

4

SOLDER TAILS MUST FIT HOLE PATTERN AS SHOWN ON THE RECOMMENDED P.C. BOARD LAYOUT.

5

PART NUMBER IS OBSOLETE.

5

113.66
[4.475]

101.60
[4.000]

—40—

101.60
[4.000]

—40—

216.51
[8.524]

227.33
[8.950]

234.95
[9.250]

246—

533514—9

5

—

—

—

—

—

—

—

—

533514—8

5

—

—

—

—

—

—

—

—

533514—7

5

149.22
[5.875]

137.16
[5.400]

54

137.16
[5.400]

54

287.63
[11.324]

298.45
[11.750]

306.07
[12.050]

330

533514—6

5

141.60
[5.575]

129.54
[5.100]

—51—

129.54
[5.100]

—51—

272.39
[10.724]

283.21
[11.150]

290.83
[11.450]

312—

533514—5

5

133.98
[5.275]

121.92
[4.800]

—48—

121.92
[4.800]

—48—

257.15
[10.124]

267.97
[10.550]

275.59
[10.850]

294—

533514—4

5

126.36
[4.975]

114.30
[4.500]

45

114.30
[4.500]

45

241.91
[9.524]

252.73
[9.950]

260.35
[10.250]

276

533514—3

5

—

—

—

—

—

—

—

—

533514—2

111.12
[4.375]

99.06
[3.900]

39

99.06
[3.900]

39

211.43
[8.324]

222.25
[8.750]

229.87
[9.050]

240

533514—1

K

G

F

E

D

C

B

A

POSN

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
R. K. SEIFRIED
06/20/90

CHK
G. SKIPPER
06/20/90

APVD
—

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± 0.13 [.005]
4 PLC ± —
ANGLES ± —

MATERIAL

1

2

FINISH

3

TE Connectivity

NAME

HDI, 3 ROW, RECEPTACLE ASSEMBLY,
1 GUIDE PIN, 3 MOUNTING HOLES, 3.05[.120]
LONG SOLDER TAILS

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

WEIGHT

—

A1

00779

533514

—

CUSTOMER DRAWING

SCALE 4:1

SHEET 2 OF 2

REV G

4805 (1/15)