





- Rating: 5A/125VAC
- Insulation resistance: 100MΩ > 500VDC
- Dielectric strength: 1000VAC for 1 minute
- Contact resistance: <50mΩ
- Life cycling (full load): 100,000 cycles

- Switching timing: non-shorting
- Life cycling (no load): 1,000,000 cycles
- Operating temperature: $-5^{\circ}\text{C} \sim +70^{\circ}\text{C}$

Mouser Stock No.	L (In.)	Travel (In.)	Oper. Force	Terminal Type
101-1201-EV	.571	.079	28g	Solder Lug
101-1202-EV	.650	.087	25g	Solder Lug
101-1203-EV	.890	.126	18g	PC Pin
101-1206-EV	1.69	.224	10a	PC Pin

- RoHS Compliant

101-1201-EV, 101-1202-EV, 101-1203-EV, 101-1206-EV

Mountain Switch

www.mouser.com 1-800-346-6873

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[101-1202-EV](#) [101-1201-EV](#) [101-1206-EV](#) [101-1203-EV](#)