





Terminal blocks

to Type 476

-  **ASP045** page 49
-  **Type 313** page 96
-  **Type 314** page 96
-  **Type 349** page 94
-  **Type 350** page 94

to Type 029

-  **Type 009** page 93
-  **Type 026** page 129
-  **Type 049** page 93

Type 476

Header, centerline 5 mm / 0.197 inches, horizontal mounting, designed for THR, optional Tape on Reel packaging for automated processing, square contact pins 1 mm / 0.039 inches, codable, open ends

Technical Data



250 V / 4 kV / 10 A

Insulation co-ordination according to EN 60664-1

Clearance and creepage distances min. 4 mm

Insulating material class CTI 600

Overvoltage category III III II

Pollution degree 3 2 2

Rated voltage 320 800 800

Rated test voltage 4 6 4

Protection category according to IEC 529

IP00

Solder pin dimension 1.0 x 1.0 mm

Recommended pc board hole dia.

Ø 1.5 mm


Solder pin length 3.4 mm

Pole size 2 - 12

Color black

Dimensions in mm

1 mm = 0.0394 in.



$L = (\text{pole size} - 1) \times \text{centerline} + 5 \text{ mm} / 0.197 \text{ inches}$

Part numbers (P/N)

(information: page 110)

Complete the part number by adding the pole size.

Type 476

centerline 5 mm / 0.197 inches

P/N 314761

		02	03	04	05	06	07	08
	09	10	11	12				

Type 029

Header, centerline 5 mm / 0.197 inches, horizontal mounting, round contact pins 1.3 mm / 0.051 inches, open ends

Technische Daten



V / A 300 / 10



V / A 300 / 10



250 V / 4 kV / 10 A

Insulation co-ordination according to EN 60664-1

Clearance and creepage distances min. 3.7 mm

Insulating material class CTI 600

Overvoltage category III III II

Pollution degree 3 2 2

Rated voltage 250 630 630

Rated test voltage 2.5 6 4

Protection category according to IEC 529

IP00

Solder pin dimension 1 mm

Recommended pc board hole dia.

Ø 1.3 mm


Solder pin length 3.6 mm

Pole size 2 - 22

Color black

Dimensions in mm

1 mm = 0.0394 in.



$L = (\text{pole size} - 1) \times \text{centerline} + 5 \text{ mm} / 0.197 \text{ inches}$

Part numbers (P/N)

(information: page 110)

Complete the part number by adding the pole size.

Type 029

centerline 5 mm / 0.197 inches

P/N 310291

		02	03	04	05	06	07	08
	09	10	11	12	13	14	15	16
	17	18	19	20	21	22		

 Standard pole sizes

 Available on demand. Minimum order quantity 5000 pieces per item.

 Standard pole sizes

 Available on demand. Minimum order quantity 5000 pieces per item.