

MIL-F-19207 military qualified panel-mount fuse holders

		* Bussmann™ series					
Military specification	Government designation	commercial equivalent	Electrical ratings	Fuse family accommodated	Knob Type	Number of poles	Max. panel thickness
MIL-F-19207/1	FHL10U	HGA-C	30 A, 90-250 V	F02, F03	Clear, neon, F-S	2	1/8"
MIL-F-19207/1	FHL10G	—					
MIL-F-19207/2	FHL11U	HGB-C					
MIL-F-19207/2	FHL11G	—					
MIL-F-19207/3	FHL12U	HGC Series					
MIL-F-19207/3	FHL12G	—		F60, F07, F09	Clear, neon, Oct.		
MIL-F-19207/8	FHL17G1	HKL	20 A, 90-250 V				
MIL-F-19207/9	FHL18G1-1	HKX	20 A, 12-22 V	F02, F03	Amber, incandescent, F-S	1	1/16"
MIL-F-19207/9	FHL18G1-2		20 A, 23-33 V				
MIL-F-19207/9	FHL18G1-3		20 A, 34-45 V				
MIL-F-19207/9	FHL18G1-4		20 A, 46-60 V				
MIL-F-19207/9	FHL18G1-5		20 A, 61-80 V				
MIL-F-19207/9	FHL18G1-6		20 A, 81-90 V				
MIL-F-19207/9	FHL18G1-7		20 A, 2.5-4 V				
MIL-F-19207/9	FHL18G1-8		20 A, 5-7 V				
MIL-F-19207/9	FHL18G1-9		20 A, 8-12 V				
MIL-F-19207/10	FHN19G†	HCM	15 A, 250 V	F05, F06	Bayonet		
MIL-F-19207/11	FHN20G	HTA	20 A, 250 V	F02, F03			
MIL-F-19207/12	FHL22W†	HPF-C	15 A, 250 V	F10	Clear		
MIL-F-19207/13	FHN23W†	HPC-D	30 A, 500 V	F60, F09	Screw		
MIL-F-19207/16	FHN26G1	HKP	30 A, 250 V		Bayonet	2	1/8"
MIL-F-19207/18	FHL29G-1	HGN-CI	30 A, 12-22 V	F02, F03	Amber, incandescent, F-S		
MIL-F-19207/18	FHL29G-2		30 A, 23-33 V				
MIL-F-19207/18	FHL29G-3		30 A, 34-45 V				
MIL-F-19207/18	FHL29G-4		30 A, 46-60 V				
MIL-F-19207/18	FHL29G-5		30 A, 61-80 V				
MIL-F-19207/18	FHL29G-6		30 A, 81-90 V				
MIL-F-19207/19	FHL30G-1	HGF-C	30 A, 12-22 V			1	1/16"
MIL-F-19207/19	FHL30G-2		30 A, 23-33 V				
MIL-F-19207/19	FHL30G-3		30 A, 34-45 V				
MIL-F-19207/19	FHL30G-4		30 A, 46-60 V				
MIL-F-19207/19	FHL30G-5		30 A, 61-80 V				
MIL-F-19207/19	FHL30G-6		30 A, 81-90 V				
MIL-F-19207/20	FHN31G1†	HJM	5 A, 250 V	F01	Bayonet		1/16"
MIL-F-19207/26	FHN42W	HWA-AF	5 A, 125 V	FM01	—	2	1/8"
MIL-F-19207/36	FHN55W	HKP/RFI	30 A, 250 V	F02, F03	RFI Shield		
MIL-F-19207/38	FHL57G	—	15 A, 125 V	F77A	Clear, neon, F-S		

Designation/description

FHL = Indicating holder
FHN = Non-indicating holder
F-S = Flat-sided knob
G = Drip proof
Oct. = Octagonal knob
U = Unsealed
W = Waterproof

* Commercial equivalent part number is for basic design reference only, NOT intended to be used as a substitute for the military part number.

† These government designations are obsolete. Their appearance in this table is for historical reference only.



Powering Business Worldwide

The only controlled copy of this data sheet is the electronic read-only version located on the Eaton network drive. All other copies of this document are by definition uncontrolled. This bulletin is intended to clearly present comprehensive product data and provide technical information that will help the end user with design applications. Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
Eaton.com

Bussmann Division
114 Old State Road
Ellisville, MO 63021
United States
Eaton.com/bussmannseries

© 2018 Eaton
All Rights Reserved
Printed in USA
Publication No. 1214 — BU-SB08838
September 2018



Eaton and Bussmann are valuable trademarks of Eaton in the US and other countries. You are not permitted to use the Eaton trademarks without prior written consent of Eaton.

For Eaton's Bussmann series product information, call **1-855-287-7626** or visit: **Eaton.com/bussmannseries**

Follow us on social media to get the latest product and support information.

