






1. MATERIALS:
HOOD: PBT GF UL94 V-0 BLACK
FRONTSEALING: SILICONE VMQ BLUE
SCREW: STAINLESS STEEL
O-RING: NBR BLACK
2. TEMPERATURE RANGE: -30°C TO +90°C
3. RECOMMENDED TORQUE FOR SCREW:
35Ncm (3.1 in.LB)
MAX. TORQUE: 68Ncm (6 in.LB)
4. SINGLE PACKED

* COMPLETELY TIGHTENED

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND				tolerance ±0,3 unless otherw. specified		 dim. in mm	scale: 1,5:1 (1:1)			
					date		name	material: SEE NOTES		
					drawn	06.02.2014	Heinrich	title: WATER RESISTANT D-SUB HOOD 25 POS. JACKSREW 4-40UNC STAINLESS STEEL		
					appd.	06.02.2014	Huether			
					norm					
					d-old	15K1A1152				
								dwg no:		DIN- A3
	a	Origin						15K1A1433		sh: 1
	rev.	description	date	name				part no:		15-004680

Directive 2002/95/EC RoHS compliant